

## Ring bolt incl. Key

Screwable sling point, 360° rotation

CARTEC

### Application:

For the safe attachment of loads.

### Execution:

- Forged, high-strength annealed
- 100% Magnaflux crack-tested in accordance with DIN EN 1677-1
- captive hexagon socket screw,
- can be rotated 360°
- designed for up to 20,000 strokes at full load
- Powder-coated surface: salmon-coloured

### Advantage:

- 4-fold safety
- Can be set in the direction of force to avoid accidental unscrewing or overscrewing
- Tool-free assembly

### Delivery:

Includes Key



<b>Art. no.</b>	<b>77232 210</b>
<b>Brand</b>	CARTEC
<b>Manufacturer Part Number</b>	C807XCHT10
<b>Design</b>	With key
<b>Thread dimension</b>	M10
<b>Load-carrying capacity</b>	0.4 t
<b>Distance between lower edge of retainer holder and retainer</b>	33.7 mm
<b>Bracket width</b>	9.8 mm
<b>Bracket height</b>	10 mm
<b>Outer diameter</b>	46 mm
<b>Diameter 2</b>	30 mm
<b>Internal width</b>	25 mm
<b>Width of support plate</b>	25.5 mm
<b>Usable thread length</b>	15 mm
<b>Width across flats</b>	6 mm
<b>Weight</b>	0.12 kg
<b>Gross Weight</b>	0.161 kg
<b>Product Group</b>	775

### EAN

8013429916724