





 $\epsilon$ 







#### **Model Number**

#### OBT300-R100-EP-IO-V3-L

Triangulation sensor (BGS) with 3-pin, M8 x 1 connector

#### **Features**

- Miniature design with versatile mounting options
- DuraBeam Laser Sensors durable and employable like an LED
- Extended temperature range -40°C ... 60°C
- High degree of protection IP69K
- IO-link interface for service and process data

# **Product information**


The R100 series miniature optical sensors are the first devices of their kind to offer an end-to-end solution in a small single standard design — from thru-beam sensor through to a distance measurement device. As a result of this design, the sensors are able to perform practically all standard automation tasks.

The entire series enables sensors to communicate via IO-Link.

The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

The use of Multi Pixel Technology gives the standard sensors a high level of flexibility and enables them to adapt more effectively to their operating environment.

#### **Dimensions**



# **Electrical connection**




#### **Pinout**

Wire colors in accordance with EN 60947-5-2



BN BU

# Indicators/operating means



- Light-on / dark-on changeover switch
- 2 Sensing range adjuster
- 3 Operating indicator / dark on
- 4 Signal indicator
- Operating indicator / light on

### **Technical data**

General	specifications
---------	----------------

7 ... 300 mm Detection range Detection range min. 7 ... 25 mm Detection range max 7 ... 300 mm Adjustment range 25 ... 300 mm

standard white, 100 mm x 100 mm Reference target

Light source laser diode

modulated visible red light Light type

Laser nominal ratings

Note LASER LIGHT, DO NOT STARE INTO BEAM

Laser class Wave length

Beam divergence > 5 mrad d63 < 1 mm in the range 150-250 mm

Pulse length 3 µs

Repetition rate approx. 13 kHz max. pulse energy 10.4 nJ Black/White difference (6 %/90 %) < 5 % at 150 mm

Diameter of the light spot approx. 1 mm at a distance of 200 mm

Angle of divergence approx. 0.3 °

Ambient light limit EN 60947-5-2: 40000 Lux

Functional safety related parameters

 $MTTF_d$ 560 a Mission Time (T<sub>M</sub>) 20 a 0 % Diagnostic Coverage (DC)

Indicators/operating means

Operation indicator LED green:

constantly on - power on flashing (4Hz) - short circuit

flashing with short break (1 Hz) - IO-Link mode

Function indicator

constantly on - object detected constantly off - object not detected Light-on/dark-on changeover switch

Control elements

Control elements Sensing range adjuster

**Electrical specifications** 

Operating voltage 10 ... 30 V DC  $\mathsf{U}_\mathsf{B}$ Ripple max. 10 %

No-load supply current  $I_0$ < 20 mA at 24 V supply voltage

Protection class

Interface

IO-Link (via C/Q = pin 4) Interface type Device profile Transfer rate COM 2 (38.4 kBaud) IO-Link Revision 1.1

Min. cycle time 2.3 ms Process data witdh

Process data input 1 Bit Process data output 2 Bit

SIO mode support

Device ID 0x110602 (1115650)

Compatible master port type Output

Switching type The switching type of the sensor is adjustable. The default set-

300 μs

C/Q - Pin4: NPN normally open / light-on, PNP normally closed /

dark-on, IO-Link

1 push-pull (4 in 1) output, short-circuit protected, reverse pola-Signal output

rity protected, overvoltage protected

max. 30 V DC Switching voltage

Switching current max. 100 mA, resistive load DC-12 and DC-13 Usage category

Voltage drop  $U_d$ ≤ 1.5 V DC Switching frequency 1650 Hz

Response time **Ambient conditions** 

Ambient temperature -40 ... 60 °C (-40 ... 140 °F)

Storage temperature -40 ... 70 °C (-40 ... 158 °F)

Mechanical specifications

www.pepperl-fuchs.com

Degree of protection IP67 / IP69 / IP69K Connection M8 x 1 connector, 3-pin

Material

Mass

Housing PC (Polycarbonate) Optical face **PMMA** 

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Laserlabel



#### CLASS 1 LASER PRODUCT

IEC 60825-1: 2007 certified. Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50. dated June 24, 2007

# CLASS 1 LASER PRODUCT

IEC 60825-1: 2007 certified. Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007

#### **Accessories**

#### IO-Link-Master02-USB

IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection

#### V3-WM-2M-PUR

Cable socket, M8, 3-pin, PUR cable

Other suitable accessories can be found at www.pepperl-fuchs.com



approx. 10 g

# Compliance with standards and directives


Directive conformity	
EMC Directive 2004/108/EC	EN 60947-5-2:2007+A1:2012
Standard conformity	
Product standard	EN 60947-5-2:2007+A1:2012 IEC 60947-5-2:2007 + A1:2012
Standards	UL 60947-5-2: 2014 IEC 61131-9:2013 IEC 60825-1:2007 EN 60825-1:2007 EN 61131-9:2013


# Approvals and certificates


UL approval E87056, cULus Listed, class 2 power supply, type rating 1

FDA approval IEC 60825-1:2007 Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007


# **Curves/Diagrams**







# **Functions and Operation**



- 1 Light-on / dark-on changeover switch
- 2 Sensing range / sensitivity adjuster
- 3 Operating indicator / dark on
- 4 Signal indicator
- 5 Operating indicator / light on

To unlock the adjustment functions turn the sensing range /sensitivity adjuster for more than 180 degrees.

# Sensing Range / Sensitivity

Turn sensing range / sensitivity adjuster clockwise to increase sensing range / sensitivity.

Turn sensing range / sensitivity adjuster counter clockwise to decrease sensing range / sensitivity.

If the end of the adjustment range is reached, the signal indicator starts flashing with 8 Hz.

#### Light-on / Dark-on Configuration

Press the light-on / dark-on changeover switch for more than 1 second (less than 4 seconds). The light-on / dark-on mode changes and the operating indicators are activated accordingly.

If you press the light-on / dark-on changeover switch for more than 4 seconds, the light-on /dark-on mode changes back to the original setting. On release of the light-on / dark-on changeover switch the current state is activated.

# **Restore Factory Settings**

Press the light-on / dark-on changeover switch for more than 10 seconds (less than 30 seconds) until all LEDs turn off. On release of the light-on / dark-on changeover switch the signal indicator turns on. After 5 seconds the sensor resumes operation with factory default settings.

After 5 minutes of inactivity the sensing range / sensitivity adjustment is locked. In order to reactivate the sensing range / sensitivity adjustment, turn the sensing range /sensitivity adjuster for more than 180 degrees.