

## Hi-res M thread plug gauge with depth measurement

for standard metric ISO thread, vernier scale 0.1 mm

leitech

### Application:

For testing threads and measuring thread depths in one pass.

### Execution:

- Thread inserts hardened and ground
- Black anodised aluminium housing
- Direct reading of the thread depth
- Measuring depth gradation of 0.1 mm using vernier scale, additional clamping of scale sleeve



<b>Art. no.</b>	<b>32851 050</b>
<b>Brand</b>	LEITECH
<b>Manufacturer Part Number</b>	303805
<b>Thread type</b>	Metric thread
<b>Type</b>	Vernier scale/hi-res
<b>Thread type x nominal diameter x pitch</b>	M5 x 0.8
<b>Tolerance class</b>	6H
<b>Handle size</b>	T 300
<b>Measuring depth</b>	25 mm
<b>Reading Length Metrology</b>	0,1 mm
<b>DIN</b>	13
<b>Gross Weight</b>	0.068 kg
<b>Product Group</b>	324