

## Collet chuck extension

With internal cooling and straight shank

**diebold**

### Application:

For clamping tools with a straight shank.

### Execution:

- With straight shank, type ER standard.
- Particularly slim version for use in milling chucks as tool extension for deep machining operations where space is restricted.
- Wrench no. 23308 008 and collets 23320.
- Wrench no. 23308 008 and collets 23320.

### Delivery:

1x collet chuck extension.



<b>Art. no.</b>	<b>23304 160</b>
<b>Brand</b>	DIEBOLD
<b>Manufacturer Part Number</b>	74.010.160
<b>Collet type</b>	ER 16
<b>Shank diameter</b>	16 mm
<b>Min./max. clamping range</b>	0.5-10 mm
<b>Width across flats</b>	25 mm
<b>Outer diameter</b>	28 mm
<b>Shaft length</b>	100 mm
<b>Length of head</b>	36 mm
<b>Gross Weight</b>	0.249 kg
<b>Product Group</b>	2AB