

2102087-1 ✓ ACTIVE

Fortis Zd

TE Internal #: 2102087-1

High Speed Backplane Connectors, Board-to-Board, 60 Position,
Row-to-Row Spacing 1.4 mm [.05 in], 6 Row, 10 Column, PCB
Mount Header

[View on TE.com >](#)



Connectors > PCB Connectors > Backplane Connectors > High Speed Connectors



Connector System: **Board-to-Board**

Number of Positions: **60**

Row-to-Row Spacing: **1.4 mm [.05 in]**

Mating Alignment: **Without**

Number of Rows: **6**

Features

Product Type Features

Connector System	Board-to-Board
PCB Connector Assembly Type	PCB Mount Header
Shroud Style	Partially Shrouded
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	60
Number of Rows	6
Number of Columns	10
Backplane Architecture	Traditional Backplane
PCB Mount Orientation	Right Angle
Guide Location	Center

Contact Features

Contact Current Rating (Max)	1.5 A
------------------------------	-------

Mechanical Attachment

Mating Alignment	Without
Connector Mounting Type	Panel Mount

Housing Features

Number of Shrouded Sides	2
--------------------------	---



Centerline (Pitch) .08 mm[1.9 in]

Dimensions

Row-to-Row Spacing 1.4 mm[.05 in]

Usage Conditions

Operating Temperature Range -65 – 125 °C[-85 – 257 °F]

Operation/Application

Circuit Application Signal

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU Not Compliant

EU ELV Directive 2000/53/EC Not Compliant

China RoHS 2 Directive MIIT Order No 32, 2016 Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006
 Current ECHA Candidate List: JAN 2021 (211)
 Candidate List Declared Against: JAN 2021 (211)
 SVHC > Threshold:
 Pb (2% in plating)
Article Safe Usage Statements:
 Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #521384-8
ASSY PL R/A RAST5 HEADER 08-D



TE Part #2102093-1
Fortis Zd 2Pr 10Col Vert Cent Mod
Assy




TE Part #2102086-1
Fortis Zd 2Pr 10Col R/A Left Module
Assy



TE Part #2-208224-3
CPC RECPT ASSEMBLY SIZE 23-37



TE Part #213780-3
CPC RECPT ASSEMBLY SIZE 23-24



TE Part #449379-2
AMPLIMITE,CONT,PWR 8,STR,POST,
AU



TE Part #1623454-1
CRG1206 1% 1R8



TE Part #3-352009-0
Hard Metric Male Connector:
Traditional Backplane, Mezzanine,
2mm



TE Part #2102088-1
Fortis Zd 2Pr 10Col R/A Rght Module
Assy



TE Part #DBC50H-12-8PN
HERM RECP

Documents

Product Drawings

[Fortis Zd 2Pr 10Col R/A Cent Module Assy](#)

English

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG_CVM_CVM_2102087-1_B.2d_dxf.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_2102087-1_B.3d_igs.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_2102087-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



Fortis Zd LRM

English

Product Specifications

Application Specification

English