


KEMET Part Number: HP55CB103JN
(HP55CB103J, HP55CW103JN)

Capacitor, ceramic, 0.01 uF, +/-5% Tol, 100V, X7R, Lead Spacing=0.2"



Dimensions (in)

Symbol	Dimension	Tolerance
L	0.2	MAX
H	0.2	MAX
T	0.1	MAX
S	0.2	+/-0.03
LL	1.25	MIN
F	0.025	NOM

Packaging Specifications

Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	1

General Information

Supplier:	KEMET
-----------	-------

Specifications

Capacitance:	0.01 uF
Lead Spacing:	0.2"
Voltage:	100V
Temperature Coefficient:	X7R
Tolerance:	+/-5%
Application:	Commercial High Temp
Temperature Range:	-55/+200C
Body Type:	Radial Conformal (Dipped)
Lead Type:	Standard Leads
Lead Form:	Straight
Termination Type:	Nickel