

#### MECHANICAL SPECIFICATIONS

- Mechanical rotation angle:  $265^{\circ} \pm 5^{\circ}$ - Electrical rotation angle: 240° ± 20°

- Torque: 0.5 to 2.5 Ncm. (0.7 to 3.4 in-oz)

- Stop torque: > 10 Ncm. ( >14 in-oz)

- Life\*: Up to 10K cycles

# PTC-15 15 mm Cermet Potentiometer

#### **FEATURES**

- Cermet resistive element.
- Plastic material according to UL94V-0..
- Alumina substrate.
- IP54 protection according to IEC 60529.
- Also upon request:
- · Wiper positioned at 50% or fully clockwise.
- Long life model for low cost control pot. applications
- · Supplied in magazines for automatic insertion.
- · Low torque option
- · Available as SPDT switch
- · Laser trimming for tighter tolerances
- · Mechanical detents
- · Special tapers

#### **ELECTRICAL SPECIFICATIONS**


- Range of values\*

 $100\Omega \le Rn \le 5 M$  (Decad. 1.0 - 2.0 - 2.2 - 2.5 - 4.7 - 5.0)

- Tolerance (\*):  $100\Omega \le Rn \le 1M \Omega = \pm 20\%$  $1M\Omega$  < Rn  $\leq$  5M  $\Omega$  .....  $\pm$  30%

- Max. Voltage: 250 VDC (lin) 125 VDC (no lin)
- Nominal Power 70°C (158°F) (see power rating curve) 0.50 W (lin) 0.25 W (no lin)
- Taper (\*) (Log. & Alog. only Rn ≥1K) Lin; Log; Alog.
- Residual resistance\*:  $\leq 0.5 \%$  Rn (5  $\Omega$  min.)
- Equivalent Noise Resistance:  $\leq 3\%$  Rn (3  $\Omega$  min.)
- Operating temperature: -40°C + 90°C (-40°F + 194°F)

\* Others upon request.



#### NOTES:

- "Z" adjustment only available on "H" versions. Standard colour for the "T" rotor: Orange (1)
- Terminals styles: "P" are crimped terminals. V=Vertical adjust; H=Horizontal Adjust (2)
- (3)Example: Code: 100  $\Omega$

Numb of zeros First two digits of the value.

000 = CM: SPDT switch 45°

(4) Non standard tolerance, upon request. Example: +7%

Code: 07 negative tolerance positive tolerance

(6)Colour shaft/rotor:

Life • Standard: 100 cycles

(5)

(7)

- Long life: 10K cycles · Potentiometer without shaft: only rotor
  - Potentiometer with shaft: only shaft
- Low Torque: ≤1.5Ncm. No detent option available for low torque models
- Magazines (35 pcs/mag): available for VA (12.5), V (12.5), V (12.5P), V (15), V15 (P) and H models. For more information please contact your nearest Piher supplier.
- If you wish to use your own custom plastic shaft/knob/actuator please contact Piher for advice about compatible materials.

NOTE: The information contained here should be used for reference purposes only.



#### HOW TO ORDER CUSTOM DRAWING


#### STANDARD OPTIONS


PTC-15 LH 01 + DRAWING NUMBER (Max. 16 digits)

This way of ordering should be used for options which are not included in the "How to order" standard and optional extras.


Detents	None
Rotor colour	Natural
Shaft colour	Natural
Wiper position	Initial
Torque	Standard
Life	100 cycles

#### **ROTORS**








### HORIZONTAL MOUNTING - VERTICAL ADJUSTMENT




### HORIZONTAL MOUNTING - VERTICAL ADJUSTMENT



















### **DETENT DETAILS**

13 detents example











### **CRIMPED TERMINALS (DETAIL)**

### **POWER RATING CURVE**












### **TAPER**

### POSITIONING

Please note relative terminal positions when ordering non linear tapers.









Std. Position = CCW

#### STANDARD SWITCH VERSION

SPDT Switch







#### SW Standard specs.

Power Rating: 24V / 15mA

ON position resistance:  $\leq$  5  $\Omega$ 

Insulation Resistance:  $\geq$  30  $\text{M}\Omega$ 


Please contact Piher for ordering information.

TYPICAL VARIATIONS **TESTS** 

ELECTRICAL LIFE	1.000 h. @ 70°C; 0.5 W	± 5 %
MECHANICAL LIFE (CYCLES)	100 @ 10 CPM15 CPM	± 3 % (Rn < 1 M Ω )
TEMPERATURE COEFFICIENT	–40° C; +90° C	± 100 ppm (Rn <100 K)
THERMAL CYCLING	16 h. @ 90° C; 2h. @ –40° C	± 2.5 %
DAMP HEAT	500 h. @ 40° C @ 95% HR	± 5 %
VIBRATION (for each plane X,Y,Z)	2 h. @ 10 Hz 55 Hz.	± 2 %

NOTE: Out of range values may not comply these results.

### **SHAFTS**



- A = Length (FRS) B = Knurling length
- C = Hollow depth
- D = Shaft diameter FRS = From rotor surface

FIG.	Α	В	С	D	Ref.
1	12	9	8	6	5272
2	19	9	15	6	5214
5	9.5	6.5	5.5	6	5208
9	35	9	31	6	5216
10	37.8	9	33.8	6	5218
11	35	25	15	6	5209
13	7.8	4.8	3.8	6	5265





FIG.	Α	В	D	Ref.
6	15	9	6	5219
7	16.8	9	6	5220
8	25.3	9	6	5207
12	46	5	6	5227

Slott (1 x 1.4) perpendicular to wiper position. Fig. 12 slot is on line with wiper position.

### **RECOMMENDED CONNECTIONS**


Recommended connection scheme for Piher's position sensors (voltage divider)



By default shafts, knobs & & thumweels are delivered unassembled.

Mounted shafts, knobs & thumbweels are delivered at random position. Positioning available upon request.

If you wish to use your own plastic shaft/knob/actuator please contact Piher for advice about compatible materials.







Fig. 27 / Ref. 5268\* Fig. 28 / Ref. 6055

#### **THUMBWHEEL**

By default shafts, knobs & & thumweels are delivered unassembled.

Mounted shafts, knobs & thumbweels are delivered at random position. Positioning available upon request.

If you wish to use your own plastic shaft/knob/actuator please contact Piher for advice about compatible materials.



<sup>\*</sup> Not available in self extinguishable plastic

#### **DETENT CONFIGURATIONS EXAMPLES**

This innovative PT's with detents family has been specifically developed to allow the integration of otherwise large and expensive external mechanisms into the body of the potentiometer thus allowing a high range of configurations: special tapers, torque, tolerances, linearity, cut track, etc.


This detent design not only adds a "click" sensation of position, but also offers enormous savings in both cost and space for any given application.

Strong and weak detents can be mixed as per customer's request.

Detent number and positions can be made or fitted to the customer needs or preferences.

Relative detent positions along the total mechanical travel.
Unless otherwise specified the detents are evenly spaced (using the end points as reference)

\*For more than 13 detents versions please contact your nearest PIHER distributor. Mechanical and/or electrical features may be affected by detents. Detents may not be available for all mounting methods. Please see our separate PTs with detents datasheet at www.piher.net



### **DETENTS WITH CONSTANT VALUE ZONES**

application

PIHER's potentiometers may feature special stepped outputs or 'constant voltage zones' for the 10mm and 15mm product families.


These constant voltage zones can be combined with PIHER's mechanical detents to provide exact alignment between the electrical output (flat areas) and the mechanical detent's positions. The result is a higher level of precision in controlling lighting, temperature, motor or other electronic control systems.

In addition to established catalogue detent configurations, we will design and manufacture any other configuration on our tried-and-tested carbon/cermet & THM/SMD potentiometer technology and processes.


With its exacting control capabilities, our 10mm and 15mm potentiometers series are well suited for many consumer applications such as ovens, ranges, dishwashers, lighting (dimmers), power hand tools, washing machines and HVAC systems.

## Constant value zones can be combined with strategically located stops matching the flat areas of the output.

10 stepped outputs version example:



#### Improved repeatability



By combining the constant value zones with the detents, engineers can align the same voltage values with each of the detent stops when rotating the control both forward and backward.

This provides clear mechanical positions that are not only repeatable, but perfectly aligned electrical outputs at each of the (detent) angles.

Piher's detents also prevent output values from changing due to vibration or accidental rotor movements, furthering reliable control consistency.

#### Design tip. Cost-effectiveness

Absolute encoders can easily be replaced connecting the potentiometer to the microprocessor's analogue input.

#### Main advantages

- ✓ Unique, non-overlapping values at each stop (detent position)
- ✓ Prevents output value change due to light vibration or accidental rotor micro-movements
- Fully customisable according to customer's needs
- ✓ Cost effective replacement for absolute encoders

#### Disclaimer

The product information in this catalogue is for reference purposes. Please consult for the most up to date and accurate design information.

Piher Sensors & Controls S.A., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Piher"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product described herein.

Piher disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Piher's terms and conditions of sale, including but not limited to the warranty expressed therein, which apply to these products.

No licence, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Piher.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Piher products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Piher for any damages arising or resulting from such use or sale. Please contact authorised Piher personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Information contained in and/or attached to this catalogue may be subject to export control regulations of the European Community, USA, or other countries. Each recipient of this document is responsible to ensure that usage and/or transfer of any information contained in this document complies with all relevant export control regulations. If you are in any doubt about the export control restrictions that apply to this information, please contact the sender immediately. For any Piher International Corp. Exports, Note: All products / technologies are EAR99 Classified commodities. Exports from the United States are in accordance with the Export Administration Regulations. Diversion contrary to US law is prohibited.









