

# 20% LEMON DETERGENT

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

Date of issue: 08/11/2016

Revision date: 05/06/2015

Version: 10.0

20% LEMON DETERGENT

33-103

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product form : Mixture  
Product name : 20% LEMON DETERGENT  
Product code : 33-103  
Type of product : Technical product

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

##### 1.2.1. Relevant identified uses

Main use category : Professional use  
Industrial/Professional use spec : For professional use only  
Use of the substance/mixture : Washing up liquid

##### 1.2.2. Uses advised against

No additional information available

#### 1.3. Details of the supplier of the safety data sheet

**ARROW COUNTY SUPPLIES** ARROW HOUSE, LONGDEN ROAD, SHREWSBURY, SY3 9AE, UNITED KINGDOM  
Tel: 01743 283600 Fax: 01743 283601 Email: purchasing@arrowcounty.com

#### 1.4. Emergency telephone number

Emergency number : Mon to Fri 8.30am to 5.00pm - 01743 283600

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification according to Regulation (EC) No. 1272/2008 [CLP]

Skin Irrit. 2 H315

Eye Irrit. 2 H319

Full text of H-phrases: see section 16

#### 2.2. Label elements

##### Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS07

Signal word (CLP) :

Warning

Hazardous ingredients :

Benzenesulphonic acid, mono-C10-14-alkyl derivs., sodium salts, Sodium laurylether sulphate, Laureth-7

Hazard statements (CLP) :

H315 - Causes skin irritation  
H319 - Causes serious eye irritation

Precautionary statements (CLP) :

P264 - Wash hands thoroughly after handling  
P280 - Wear eye protection, protective gloves  
P302+P352 - IF ON SKIN: Wash with plenty of soap, water  
P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
P332+P313 - If skin irritation occurs: Get medical advice/attention  
P337+P313 - If eye irritation persists: Get medical advice/attention  
P362+P364 - Take off contaminated clothing and wash it before reuse

#### 2.3. Other hazards

No additional information available

### SECTION 3: Composition/information on ingredients

#### 3.1. Substance

Not applicable

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

**3.2. Mixture**

Name	Product identifier	%	Classification according to Directive 67/548/EEC	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Benzenesulphonic acid, mono-C10-14-alkyl derivs., sodium salts	(CAS No) 85117-50-6 (EC no) 285-600-2	5 - 15	Xn; R22 Xi; R41 Xi; R38	Acute Tox. 4 (Oral), H302 Skin Irrit. 2, H315 Eye Dam. 1, H318
Sodium lauryl ether sulphate	(CAS No) 68891-38-3 (EC no) 500-234-8	1 - 5	Xi; R41 Xi; R38	Eye Dam. 1, H318 Skin Irrit. 2, H315
Laureth-7	(CAS No) 160901-19-9	1 - 5	Xn; R22 Xi; R41	Acute Tox. 4 (Oral), H302 Eye Dam. 1, H318

Full text of R- and H-phrases: see section 16

**SECTION 4: First aid measures****4.1. Description of first aid measures**

- First-aid measures general : Get medical advice/attention if you feel unwell.
- First-aid measures after inhalation : Remove person to fresh air and keep comfortable for breathing.
- First-aid measures after skin contact : Wash with plenty of soap and water.
- First-aid measures after eye contact : IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
- First-aid measures after ingestion : Give nothing or a little water to drink. Get medical advice/attention if you feel unwell.

**4.2. Most important symptoms and effects, both acute and delayed**

- Symptoms/injuries after inhalation : May cause respiratory irritation.
- Symptoms/injuries after skin contact : Repeated exposure may cause skin dryness or cracking.
- Symptoms/injuries after eye contact : Causes eye irritation.
- Symptoms/injuries after ingestion : May cause a light irritation of the linings of the mouth, throat, and gastrointestinal tract.

**4.3. Indication of any immediate medical attention and special treatment needed**

Treat symptomatically.

**SECTION 5: Firefighting measures****5.1. Extinguishing media**

- Suitable extinguishing media : Carbon dioxide. Dry powder. Foam.

**5.2. Special hazards arising from the substance or mixture**

No additional information available

**5.3. Advice for firefighters**

No additional information available

**SECTION 6: Accidental release measures****6.1. Personal precautions, protective equipment and emergency procedures****6.1.1. For non-emergency personnel**

- Emergency procedures : Evacuate unnecessary personnel.

**6.1.2. For emergency responders**

- Protective equipment : Use personal protective equipment as required.

**6.2. Environmental precautions**

Avoid release to the environment.

**6.3. Methods and material for containment and cleaning up**

- For containment : Collect spillage.
- Methods for cleaning up : Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible.

**6.4. Reference to other sections**

For further information refer to section 8: "Exposure controls/personal protection". For further information refer to section 13.

**SECTION 7: Handling and storage****7.1. Precautions for safe handling**

- Precautions for safe handling : Avoid contact with eyes.
- Hygiene measures : Do not eat, drink or smoke when using this product.

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

### 7.2. Conditions for safe storage, including any incompatibilities

Technical measures	: Does not require any specific or particular technical measures.
Storage conditions	: Keep container closed when not in use.
Incompatible products	: Oxidizing agent. Strong acids. Strong bases.
Special rules on packaging	: Keep only in original container.

### 7.3. Specific end use(s)

No additional information available

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

No additional information available

### 8.2. Exposure controls

Materials for protective clothing	: Not required for normal conditions of use
Hand protection	: Protective gloves
Eye protection	: Safety glasses
Skin and body protection	: Not required for normal conditions of use
Respiratory protection	: Not required for normal conditions of use



## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Appearance	: Mobile liquid.
Colour	: Yellow.
Odour	: lemon-like.
Odour threshold	: No data available
pH	: 5
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: No data available
Flash point	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: No data available
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: 1.02
Solubility	: No data available
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

### 9.2. Other information

No additional information available

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No additional information available

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

### 10.2. Chemical stability

Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

No additional information available

### 10.4. Conditions to avoid

No additional information available

### 10.5. Incompatible materials

No additional information available

### 10.6. Hazardous decomposition products

No additional information available

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

Acute toxicity	: Not classified
Skin corrosion/irritation	: Causes skin irritation. pH: 5
Serious eye damage/irritation	: Causes serious eye irritation. pH: 5
Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified
Reproductive toxicity	: Not classified
Specific target organ toxicity (single exposure)	: Not classified
Specific target organ toxicity (repeated exposure)	: Not classified
Aspiration hazard	: Not classified

## SECTION 12: Ecological information

### 12.1. Toxicity

Laureth-7 (160901-19-9)	
LC50 other aquatic organisms 1	> 1 (1 - 10) mg/l
EC50 Daphnia 1	> 1 (1 - 10) mg/l
ErC50 (algae)	> 1 (1 - 10) mg/l

### 12.2. Persistence and degradability

No additional information available

### 12.3. Bioaccumulative potential

No additional information available

### 12.4. Mobility in soil

No additional information available

### 12.5. Results of PBT and vPvB assessment

No additional information available

### 12.6. Other adverse effects

No additional information available

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

No additional information available

## SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

### 14.1. UN number

Not regulated for transport

### 14.2. UN proper shipping name

Proper Shipping Name (ADR) : Not applicable

## Safety Data Sheet

according to Regulation (EC) No. 453/2010

Proper Shipping Name (IMDG) : Not applicable  
 Proper Shipping Name (IATA) : Not applicable

**14.3. Transport hazard class(es)****ADR**

Transport hazard class(es) (ADR) : Not applicable

**IMDG**

Transport hazard class(es) (IMDG) : Not applicable

**IATA**

Transport hazard class(es) (IATA) : Not applicable

**14.4. Packing group**

Packing group (ADR) : Not applicable

Packing group (IMDG) : Not applicable

Packing group (IATA) : Not applicable

**14.5. Environmental hazards**

Dangerous for the environment : No

Marine pollutant : No

Other information : No supplementary information available

**14.6. Special precautions for user****- Overland transport**

No data available

**- Transport by sea**

No data available

**- Air transport**

No data available

**14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code**

Not applicable

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****15.1.1. EU-Regulations**

Contains no substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

**15.1.2. National regulations****Germany**

VwVwS Annex reference : Water hazard class (WGK) 2, hazardous to water (Classification according to VwVwS, Annex 4)

12th Ordinance Implementing the Federal Immission Control Act - 12.BImSchV : Is not subject of the 12. BImSchV (Hazardous Incident Ordinance)

**15.2. Chemical safety assessment**

No additional information available

**SECTION 16: Other information**

Full text of R-, H- and EUH-phrases:

Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2

**Safety Data Sheet**

according to Regulation (EC) No. 453/2010

Skin Irrit. 2	Skin corrosion/irritation, Category 2
H302	Harmful if swallowed
H315	Causes skin irritation
H318	Causes serious eye damage
H319	Causes serious eye irritation

## SDS EU

*This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product*