

## ANNEX

EU TYPE EXAMINATION CERTIFICATE Nr. 081/2019/0564

### 1. Applicant

Showa Glove Co  
565 Tohori Himeji  
670 0802 Hyogo  
Japan

### 2. Description

EN 388:2016



1 0 0 0 X

EN ISO 374-1 / Type C



EN ISO 374-5



### 3. Materials and accessories

#### Gloves

- Showa® 7540



#### 4. Technical documentation

##### Summary test results

EN 420:2003+A1:2009      Gloves      **Showa® 7540**

Method	Description	Result	Class
EN 1413	pH - textile	PASS	
EN 14362-1	AZO dyes for colored gloves	PASS	
EN 420 length	Length	Fit for special purpose	
EN 420 dexterity	Dexterity	PASS	Level 5
1149-1 / 1149-2 / 1149-3	Electrostatic properties	/	/

EN 388:2016      Gloves      **Showa® 7540**

Method	Description	Result	Class
EN 13594:2015 §6.9	Impact Test	/	/
EN 388 6.1	Abrasion resistance	PASS	Level 1
EN 388 6.2	Cut resistance	/	Level 0
EN 388 6.4	Tear resistance	/	Level 0
EN 388 6.5	Puncture resistance	/	Level 0
ISO 13997 6.3	Cut resistance	/	X

EN ISO 374-1:2016      Gloves      **Showa® 7540**

Method	Description	Result	Class
EN 374-2	Penetration	PASS	
EN 16523-1	Permeation J	PASS	Level 6
EN 16523-1	Permeation K	PASS	Level 6
EN 16523-1	Permeation L	/	Level 0
EN 374-4	Degradation J	PASS	
EN 374-4	Degradation K	PASS	
EN 374-4	Degradation L	PASS	
Type of glove		PASS	Type C

EN ISO 374-5:2016      Gloves      **Showa® 7540**

Method	Description	Result	Class
EN 374-2	Penetration	PASS	
ISO 16604 Proc. B	Protection against viruses	/	/

## Description/Picture of article

Article **The Gloves Showa® 7540**



The above picture is a general picture of the article. Possible variations of the above article can be present in the technical file.

Note :

Any modification in material, design, or other technical features must be brought to the attention of the Notified Body.