

c(UL)us CE VISC‡ 


# **Model Number**


# MLV12-54/47/92

Retroreflective sensor with 4-pin M12 connector, 90° adjustable position

# **Features**


- ٠ Robust photoelectric sensor series in a widely used standard housing
- Resistant against noise: reliable ope-٠ ration under all conditions
- Clear and functional display concept for the operating modes
- High level of stability thanks to the me-٠ tal housing frame
- Tightly sealed thanks to welded plas-٠ tic components
- Suitable for operation at low tempera-٠ tures down to -40 °C





# **Electrical connection**

**Dimensions** 







**Pinout** 



# Indicators/operating means





1	Operating display green		
2	Switch state yellow		
3	Light/dark switch		
4	Sensitivity adjuster		
5	Optical axis emitter		
6	Optical axis receiver		

Pepperl+Fuchs Group www.pepperl-fuchs.com

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411

fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



CCC approval

Technical data			Accessories	
General specifications			OMH-MLV12-HWG	
Effective detection range		0 6.5 m	Mounting bracket for series MLV12 sen-	
Reflector distance		0.01 6.5 m		
Threshold detection range		9 m	sors	
Reference target		H85-2 reflector	OMH-MLV12-HWK	
Light source		LED	Mounting bracket for series MLV12 sen-	
Light type		modulated visible red light , 660 nm	sors	
Diameter of the light spot		approx. 170 mm at detection range 6.5 m	ОМН-К01	
Angle of divergence		1.5 °		
Ambient light limit			dove tail mounting clamp	
Continuous light		50000 Lux	OMH-K02	
Modulated light		5000 Lux	dove tail mounting clamp	
Functional safety related para	meters		dovo kai mounting olamp	
MTTF <sub>d</sub>		1000 a	ОМН-К03	
Mission Time (T <sub>M</sub> )		20 a	dove tail mounting clamp	
Diagnostic Coverage (DC)		0 %		
Indicators/operating means			OMH-06	
Operating display		LED green, flashes in case of short-circuit	Mounting aid for round steel ø 12 mm or	
Function display		2 LEDs yellow, light up when light beam is free, flash when falling short of the stability control, off when light beam is interrupted	sheet 1.5 mm 3 mm	
Controls		rotary switch for light/dark, sensitivity adjuster	Other suitable accessories can be found at	
Electrical specifications		Total y owner for light dain, concluding dajacter	www.pepperl-fuchs.com	
Operating voltage	U <sub>B</sub>	10 30 V DC		
Ripple	OB	max. 10 %		
No-load supply current	I <sub>0</sub>	max. 40 mA		
Output	0			
Switching type		light/dark on owitchable		
Signal output		light/dark on switchable 2 PNP outputs, complementary, short-circuit protected, reverse placity protected, open collector		
Switching voltage		polarity protected, open collector max. 30 V DC		
Switching voltage		max. 0.2 A		
Switching current		≤ 2.5 V DC		
Voltage drop Switching frequency	U <sub>d</sub> f	1000 Hz		
Response time	1	0.5 ms		
•		0.5 113		
Ambient conditions Ambient temperature		-40 60 °C (-40 140 °F)		
•				
Storage temperature		-40 75 °C (-40 167 °F)		
Mechanical specifications		1067		
Protection degree		IP67		
Connection		4-pin, M12 metal connector, 90° rotatable		
Material		Frame: nickel plated, dia agent zing		
Housing		Frame: nickel plated, die cast zinc, Laterals: glass-fiber reinforced plastic PC		
Optical face		Plastic pane		
Mass		60 g		
Compliance with standards a ves	nd directi	0		
Standard conformity				
Product standard		EN 60947-5-2:2007		
Shock and impact registeres		IEC 60947-5-2:2007 IEC / EN 60068. half-sine, 40 g in each X, Y and Z directions		
Shock and impact resistance Vibration resistance		IEC / EN 60068-2-6. Sinus. 10 -150 Hz, 5 g in each X, Y and Z directions directions		
Approvals and certificates				
Protection class		II, rated voltage $\leq$ 300 V AC with pollution degree 1-2 accor-		
UL approval		ding to IEC 60664-1		
		CCC approval / marking not required for products rated <36 V		

Release date: 2013-04-18 17:06 Date of issue: 2013-05-13 117836\_eng.xml

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" Pepperl+Fuchs Group USA: +1 330 486 0001

www.pepperl-fuchs.com

2


CCC approval / marking not required for products rated  $\leq$ 36 V


Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



# **Curves/Diagrams**





# Additional Information

# **Conventional use**

The reflex light beam switch contains the emitter and receiver in a single housing. The light from transmitter is beamed back from a reflector to the receiver. If an object interrupts the light beam the switching function is initiated.

# Mounting instructions

The sensor can be fastened over the through-holes directly or with a support angle or clamping components (this are not contained in the scope of supply).

The base surface must be flat to avoid distorting the housing during mounting. It is advisable to secure the bolts and screws with washers to prevent misalignment.

# Adjustment instructions

Connect the sensor to operating voltage, the LED green lights up constantly.

Mount suitable reflector opposite light beam switch and align roughly.

The exact adjustment takes by swivelling the sensor horizontally and vertically. With optimum light reception the yellow LED lights up constantly. They flash if setting is inexact.

### **Object detection check**

Move the object into the light beam. If the object is recorded, the yellow LED switch off. If it does not switch off, reduce the sensitivity with the potentiometer until the switches off. It should lights up constantly on again when the object is removed.

# Lustration

The yellow LED flashes if reception deteriorates (e.g. soiled lenses.)

We recommend that you clean the optical interfaces and check the plug- and screw connections at regular intervals.

117836 eng.xml 2013-05-13 Date of issue: Release date: 2013-04-18 17:06

