

# COMBINATION WRENCHES



EGA Master Non-Sparking Tools are the best alternative for non-sparking application purposes in potentially explosive environments.



1. The hardness is 283-365 Brinell (Cu-Be) and 229-291 Brinell (Al-Bron).



## COMBINATION WRENCHES



MM

| Cu-Be | COD   |         | AF  | L<br>mm | AF |
|-------|-------|---------|-----|---------|----|
|       | Cu-Be | Al-Bron |     |         |    |
| 70170 | 70682 | 6mm     | 115 | 35      |    |
| 70171 | 70683 | 7mm     | 120 | 40      |    |
| 70172 | 70684 | 8mm     | 125 | 45      |    |
| 70173 | 70685 | 9mm     | 130 | 60      |    |
| 70174 | 70686 | 10mm    | 135 | 65      |    |
| 70175 | 70687 | 11mm    | 140 | 70      |    |
| 70176 | 70688 | 12mm    | 145 | 85      |    |
| 70177 | 70689 | 13mm    | 155 | 95      |    |
| 70178 | 70690 | 14mm    | 165 | 100     |    |
| 70179 | 70691 | 15mm    | 175 | 110     |    |
| 70180 | 70692 | 16mm    | 185 | 150     |    |
| 70181 | 70693 | 17mm    | 195 | 160     |    |
| 70182 | 70694 | 18mm    | 200 | 190     |    |
| 70183 | 70695 | 19mm    | 210 | 210     |    |
| 70184 | 70696 | 20mm    | 220 | 240     |    |
| 70185 | 70697 | 21mm    | 230 | 260     |    |
| 70186 | 70698 | 22mm    | 240 | 280     |    |
| 70187 | 70699 | 23mm    | 250 | 350     |    |
| 70188 | 70700 | 24mm    | 260 | 380     |    |
| 70189 | 70701 | 25mm    | 270 | 400     |    |
| 70190 | 70702 | 26mm    |     | 420     |    |
| 70191 | 70703 | 27mm    | 280 | 480     |    |
| 70192 | 70704 | 28mm    | 290 | 500     |    |

| Cu-Be | COD   |         | AF  | L<br>mm | AF |
|-------|-------|---------|-----|---------|----|
|       | Cu-Be | Al-Bron |     |         |    |
| 70193 | 70705 | 29mm    | 300 | 650     |    |
| 70194 | 70706 | 30mm    | 310 | 700     |    |
| 70195 | 70707 | 31mm    | 320 | 750     |    |
| 70196 | 70708 | 32mm    | 330 | 800     |    |
| 72700 | 71786 | 33mm    |     | 850     |    |
| 72701 | 71787 | 34mm    | 340 | 950     |    |
| 70197 | 70709 | 35mm    |     | 1100    |    |
| 70198 | 70710 | 36mm    | 350 |         |    |
| 70199 | 70711 | 38mm    |     | 1200    |    |
| 70200 | 70712 | 40mm    | 370 | 1550    |    |
| 70201 | 70713 | 41mm    |     | 1750    |    |
| 70202 | 70714 | 42mm    | 430 | 2100    |    |
| 70203 | 70715 | 46mm    |     | 2200    |    |
| 70204 | 70716 | 50mm    | 460 | 2600    |    |
| 73618 | 73619 | 52mm    |     | 3000    |    |
| 70205 | 70717 | 55mm    | 470 | 3550    |    |
| 70206 | 70718 | 60mm    |     | 4100    |    |
| 70207 | 70719 | 65mm    | 490 | 4550    |    |
| 70208 | 70720 | 70mm    |     | 5350    |    |
| 70209 | 70721 | 75mm    | 500 | 5800    |    |
| 70210 | 70722 | 80mm    |     |         |    |
| 70211 | 70723 | 85mm    |     |         |    |
| 70212 | 70724 | 90mm    |     |         |    |

COMBINATION WRENCHES



INCH.

| COD   |         | AF      | L (mm) | Weight (g) |
|-------|---------|---------|--------|------------|
| Cu-Be | Al-Bron |         |        |            |
| 70725 | 70751   | 1/4"    | 115    | 25         |
| 75305 | 75306   | 9/32"   | 120    | 30         |
| 70726 | 70752   | 5/16"   | 125    | 35         |
| 70727 | 70753   | 11/32"  | 130    | 40         |
| 70728 | 70754   | 3/8"    | 135    | 55         |
| 76855 | 76856   | 13/32"  | 140    | 70         |
| 70729 | 70755   | 7/16"   | 140    | 70         |
| 70730 | 70756   | 1/2"    | 140    | 70         |
| 70731 | 70757   | 9/16"   | 165    | 95         |
| 75307 | 75308   | 19/32"  | 165    | 95         |
| 70732 | 70758   | 5/8"    | 175    | 130        |
| 70733 | 70759   | 11/16"  | 195    | 140        |
| 70734 | 70760   | 3/4"    | 210    | 200        |
| 76857 | 76858   | 25/32"  | 230    | 280        |
| 70735 | 70761   | 13/16"  | 230    | 280        |
| 70736 | 70762   | 7/8"    | 260    | 330        |
| 70737 | 70763   | 15/16"  | 260    | 360        |
| 76859 | 76860   | 31/32"  | 280    | 460        |
| 70738 | 70764   | 1"      | 280    | 460        |
| 70739 | 70765   | 1.1/16" | 280    | 460        |

| COD   |         | AF       | L (mm) | Weight (g) |
|-------|---------|----------|--------|------------|
| Cu-Be | Al-Bron |          |        |            |
| 70739 | 70765   | 1.1/16"  | 280    | 460        |
| 70740 | 70766   | 1.1/8"   | 300    | 500        |
| 72937 | 72936   | 1.3/16"  | 320    | 550        |
| 70741 | 70767   | 1.1/4"   | 350    | 700        |
| 70742 | 70768   | 1.5/16"  | 360    | 1000       |
| 70743 | 70769   | 1.3/8"   | 360    | 1150       |
| 70744 | 70770   | 1.7/16"  | 360    | 1200       |
| 70745 | 70771   | 1.1/2"   | 360    | 1200       |
| 75309 | 75310   | 1.9/16"  | 370    | 1350       |
| 70746 | 70772   | 1.5/8"   | 370    | 1350       |
| 70747 | 70773   | 1.11/16" | 370    | 1500       |
| 75311 | 75312   | 1.3/4"   | 400    | 1600       |
| 70748 | 70774   | 1.13/16" | 400    | 1600       |
| 70749 | 70775   | 1.7/8"   | 420    | 1700       |
| 70750 | 70776   | 2"       | 420    | 1700       |
| 76861 | 76862   | 2.3/16"  | 445    | 2100       |
| 76863 | 76864   | 2.3/8"   | 460    | 2400       |
| 76865 | 76866   | 2.9/16"  | 470    | 2800       |
| 76867 | 76868   | 2.5/8"   | 480    | 3300       |
| 76869 | 76870   | 2.3/4"   | 480    | 3300       |



Cu-Be beryllium copper

Al-Bron aluminium bronze