

SVLC steel boring bar, positive left

For longitudinal and copy turning with VC indexable insert

ATORN[®]



Application

For longitudinal and copy turning with VC indexable insert 55°

Version

- Precision-manufactured boring bar, **steel**, with internal cooling, type V, pitch angle 95°, tip angle 35°, clearance angle 7°

Advantage

- Slender geometry for longitudinal and copy turning
- Positive geometry for the body ensures low cutting forces

Art. No.	17827 340
ISO name	A 12K SVLC R/L 07
Min. bore diameter	15.5 mm
Shaft diameter	12 mm
Cutting edge height	8.0 mm
Clearance length	28 mm
Length	125 mm
Clamping surface height	11 mm
Programming size	9 mm
Suitable for indexable inserts	VC.. 0702..
Tool design	Left
DIN	8024

EAN-Code

4050293390575