

Internal micrometer set

ATORN[®]

Application

For measuring large bore diameters, distances on workpieces, etc.

Version

- Scale with anti-glare, brushed chromium-plated finish
- Carbide-tipped measuring faces
- Can be individually configured for the diameter being measured
- Graduated drum, Ø 17 mm
- Measuring body, 25 mm, adjustable
- Threaded connection, M7 x 1

Advantage

- Ready for measuring with no special settings required
- High level of measuring accuracy due to extension rods hardened at the ends, lapped along the length of the gauge block and with insulated grips to prevent transfer of heat from the hands
- Measuring range extendible via screw-on extensions

Delivery

In wooden case



Art. no.	31678 125
Min./max. length measuring range	50-250 mm
Digit increment	0.01 mm
Extensions provided	100 mm, 50 mm, 25 mm
DIN	863

EAN-Code

4050293402230