


TUNGSTEN HALOGEN LAMPS • MR16 REFLECTOR


JCR

- Focused Beam for Optical Applications
- Only for Use in Approved Enclosed Halogen Fixtures
- 2-Pin Base - GX5.3
- 50mm Dichroic Coated Reflector



Watts (W)	Ordering Code	Lamp Description	MOL (mm)	Reflector Type	Filament Type	Working Distance (mm)	Luminous Intensity (cd)	Center Screen Illuminance (lx)	Color Temp (K)	Avg Life (h)	Burn Position	Case Qty
2-Pin Base – GX5.3												
30	1000315	EKZ, JCR10.8V-30W	44.5	Specular	CC-6	38.1	—	400	3100	200	BD/Hor	10
35	1000344	EPN, JCR12V-35W	44.5	Specular	C-6	29.0	—	350	3300	50	BD/Hor	10
50	1000335	ENL, JCR12V-50W	44.5	Faceted	C-6	38.1	2000	—	3000	4000	Univ	10
50	1000350	EPZ, JCR13.8V-50W	44.5	Specular	CC-6	108	—	—	3150	1000	BD/Hor	10
50	1000339	ENZ, JCR30V-50W	44.5	Specular	CC-6	29.0	—	650	3400	25	BD/Hor	12
80	1000174	DDM, JCR19V-80W	44.5	Faceted	CC-6	152.4	—	680	3350	50	BD/Hor	10
80	1000303	EJY, JCR19V-80W	44.5	Specular	CC-6	38.1	—	—	3400	25	BD/Hor	12
80	1000307	EKG, JCR19V-80W	44.5	Specular	CC-6	44.5	—	700	3400	25	BD/Hor	10
80	1000336	ENW/ENC, JCR19V-80W	44.5	Specular	CC-6	44.5	—	600	3200	400	BD/Hor	10
80	1000177	DDS, JCR21V-80W	44.5	Faceted	CC-6	165.0	—	646	3125	500	BD/Hor	10
80	1000312	EKP, JCR30V-80W	44.5	Faceted	CC-6	44.5	—	750	3400	25	BD/Hor	10
80	1000317	ELB, JCR30V-80W	44.5	Specular	CC-6	29.0	—	900	3400	15	BD/Hor	12
85	1000180	DED, JCR13.8V-85W	44.5	Specular	C-8	165.0	—	1000	3150	1000	BD/Hor	10
90	1000347	EPV, JCR14.5V-90W	44.5	Stippled	CC-6	155.2	—	1345	3150	500	BD/Hor	10
90	1000349	EPX, JCR14.5V-90W	44.5	Stippled	CC-6	165.1	—	538	3150	500	BD/Hor	10
100	1000326	EMC, JCR12V-100W	44.5	Faceted	CC-6	26.5	—	—	3200	200	BD/Hor	10
100	1000420	EXV, JCR12V-100W	44.5	Faceted	C-6	—	4500	—	3350	50	BD/Hor	10
120	1000311	EKN, JCR17.7V-120W	44.5	Specular	CC-6	38.1	—	1000	3200	120	BD/Hor	10
150	1000173	DDL, JCR20V-150W	44.5	Faceted	CC-6	194.5	—	400	3150	500	BD/Hor	10
150	1001628	EKE/HO, JCR21V-150W	44.5	Specular	CC-6	43	—	—	3250	200	BD/Hor	10
150	1000297	EJA, JCR21V-150W	44.5	Specular	CC-6	28	—	—	3400	40	BD/Hor	10
150	1000301	EJM, JCR21V-150W	44.5	Specular	CC-6	38.1	—	—	3400	40	BD/Hor	10
150	1000302	EJV, JCR21V-150W	44.5	Specular	CC-6	44.5	—	1500	3400	40	BD/Hor	10
150	1000306	EKE, JCR21V-150W	44.5	Specular	CC-6	44.5	—	900	3250	200	BD/Hor	10
150	1003370	EKE/L, JCR21V-150W 10H/5	44.5	Specular	CC-6	—	—	—	—	1000	BD	10
150	1000319	ELD/EJN, JCR21V-150W	44.5	Stippled	CC-6	50.8	—	320	3400	40	BD/Hor	10
200	1000300	EJL, JCR24V-200W	44.5	Specular	CC-6	31.7	—	1100	3400	50	BD/Hor	10
200	1000314	EKX, JCR24V-200W	44.5	Stippled	CC-6	139.7	—	—	3400	25	BD/Hor	10
250	1000318	ELC, JCR24V-250W	44.5	Specular	CC-6	31.7	—	1500	3400	50	BD/Hor	10
250	1003106	ELC-3, JCR24V-250W	44.5	Specular	CC-6	31.8	—	960	3400	300	BD/Hor	10
250	1003264	ELC-5, JCR24V-250W	44.5	Specular	CC-6	31.8	—	960	3400	500	BD/Hor	10

Center Screen Illuminance - Approximate value for reference only




GX5.3

JCR

- Focused Beam for Optical Applications
- Only for Use in Approved Enclosed Halogen Fixtures
- Oval 2-Pin Base - GY5.3, 2-Pin Base - GZ6.35
- 50mm Dichroic Coated Reflector
- Operate Base Down to Horizontal



Watts	Ordering Code	Lamp Description	Dimensions (mm)		Reflector Type	Filament Type	Working Distance (mm)	Color Temp (K)	Avg Life (h)	Burn Position	Case Qty
			Dia (A)	MOL (B)							
Oval 2-Pin Base – GY5.3											
85	1000357	ESH, JCR82V-85W	50.67	44.5	Stippled	CC-8	152.0	2950	250	BD/Hor	10
85	1000358	ESJ, JER82V-85W	50.67	44.5	Specular	CC-8	32.0	3350	40	BD/Hor	10
150	1000356	ESD, JCR120V-150W	50.67	44.5	Stippled	CC-8	44.5	3350	12	BD/Hor	12
150	1000940	JCR120V-150W/B	50.67	44.5	Stippled	CC-8	—	3050	100	BD/Hor	10
200	1000441	EYA, JCR82V-200W	50.67	44.5	Faceted	CC-8	38.1	3300	50	BD/Hor	12
250	1000386	EVW, JCR82V-250W	50.67	44.5	Faceted	CC-8	298.5	3300	50	BD/Hor	10
250	1000333	ENH, JCR120V-250W	50.67	44.5	Faceted	CC-8	152.4	3250	175	BD/Hor	10
250	1000379	ETJ, JCR120V-250W	50.67	44.5	Specular	CC-8	36.5	3250	175	BD/Hor	10
300	1000321	ELH, JCR120V-300W	50.67	44.5	Stippled	CC-8	154.3	3350	35	BD/Hor	10
300	1000332	ENG, JCR120V-300W	50.67	44.5	Stippled	CC-8	152.4	3450	15	BD/Hor	10
360	1000337	ENX, JCR82V-360W	50.67	44.5	Faceted	CC-8	298.5	3300	75	BD/Hor	10
360	1000338	ENX-5, JCR86V-360W	50.67	44.5	Faceted	CC-8	298.5	3300	75	BD/Hor	10
410	1000636	FXL, JCR82V-410W	50.67	44.5	Faceted	CC-8	298.5	3300	75	BD/Hor	10
2-Pin Base – GZ6.35											
50	1000268	EFM, JCR8V-50W	49.7	42.0	—	C-6	32.0	3350	50	BD/Hor	10
75	1000270	EFN, JCR12V-75W	50.0	42.0	Specular	C-6	32.0	3400	50	BD/Hor	10
100	1000271	EFP, JCR12V-100W	50.0	42.0	Specular	C-6	32.0	3400	50	BD/Hor	10
100	1003003	JCR12V-100W/H10	50.0	42.0	Specular	C-8	32.0	3100	1000	BD/Hor	10
150	1000272	EFR, JCR15V-150W	50.0	42.0	Specular	C-8	32.0	3400	50	BD/Hor	10



GY5.3

GZ6.35