

Hinged-door cabinet with shelf and drawers

Doors with slotted panels

RasterPlan

Application:

For clearly-arranged and space-saving storage of tools.

Execution:

- Welded sheet steel structure with rear wall, ¼ slotted/¼ perforated panel for attaching support elements
- Overlay, double-walled, twist-resistant hinged doors, opening angle over 200°
- Three-point security cylinder lock with recessed turning handle



Art. no.	50639 175
Brand	RASTERPLAN
Manufacturer Part Number	1460.05.4016
Door design	Slotted plates
Width	1000 mm
Depth	600 mm
Height	1950 mm
Number of shelves	1 PCS
Shelf width	1000 mm
Shelf depth	600 mm
Load-carrying capacity per shelf	80 kg
Number of drawers	3 PCS
Drawer front height	3 x 100 mm
With worktop	Yes
Load-carrying capacity per drawer	110 kg
Pullout type	Full extension
With partition wall	No
Central locking	Yes
Lock type	Twist-grip lock with three-point fastening
Material	Sheet steel
Colour of front	Gentian blue RAL 5010
Surface	Lacquered
Cabinet colour	Light grey RAL 7035
Gross Weight	145.700 kg
Product Group	5AC

EAN

4251142217269