

Electrically operated drum pump TecPump 600 AC

Completely ready for use with suction pipe, pressure hose and tap valve



Execution:

- Electrically-operated, self-priming vane pump
- For pumping diesel, heating oil, and concentrated radiator frost protection agent
- Siphon protection/return line, barrel thread G 2"
- Suction filter in the pump chamber
- Integrated overflow valve
- 2-m connection cable, 1.6-m suction hose, 4-m pneumatic hose
- Automatic delivery valve

| | |
|---------------------------------|------------------|
| Art. no. | 56345 160 |
| Brand | HORN TECALEMIT |
| Manufacturer Part Number | 105620400 |
| Model | TecPump 600 AC |
| Max. immersion depth | 1600 mm |
| Feed quantity | 55 l/min |
| Suitable for container | 60-200 litres |
| Gross Weight | 12.100 kg |
| Product Group | 575 |



EAN

4031109012812