

B 702 705





SIL Sockets "Through hole"

2,54mm

Technical data:

Insulator: High temp. thermoplast, UL94V-0
 Contact: Brass / BeCu
 Rated current: 3 Amp.
 Rated voltage: 100 V_{RMS} / 150 V_{DC}
 Dielectric withstanding: min. 1000 V_{RMS}
 Operating temperature: -55°C to +125°C
 Max. processing temp.: 260°C for 10 seconds



MS XX S XX U

Poles: 2 - 64 poles possible

XX: TG B = sleeve: Sn, clip: Au **15 B 5800**
 GG B = sleeve: Au, clip: Au
 TG B 8 = sleeve: Sn, clip: 0,75µm Au
 GG B 2 = sleeve: Au, clip: 0,25µm Au **15 B 632**

U: RoHS-compliant