



Product Information

Product Category	OVENS
Unit Barcode	5016368055816
Outer Carton Barcode	
Commodity Code	8516608090
Country of Origin	CHINA
Primary Colour	BLACK
Finish	STAINLESS STEEL
Primary Material	STAINLESS STEEL
Warranty	2
Self Assembly	NO
Perishable Item	NO
Hazardous Item	NO

General Product Specification

Voltage	230
Frequency	50
Wattage	3000
Rated Current	13.04
Fuse Rating	
Plug Type	
Cable Diameter	1.5
Cable Length	1
Class	CLASS I
Conformity Markings	CE+UKCA

Packaging & Shipping Information

Product Dimensions H x W x D (mm)	595	595	575
Packaged Dimensions H x W x D (mm)	668	648	688
Outer Carton Dimensions H x W x D (mm)			
Outer Carton Qty.			
Unit Weight (Kg)			32
Unit Packaged Weight (Kg)			36
Carton Weight (Kg)			
EPS (Kg)	0.48	PPT Exempt Plastic (Kg)	
Other Plastic (Kg)	0.649	Card / Paper (Kg)	2.87
Aluminium (Kg)		Steel (Kg)	0.007

Category Specific Technical Information

Timer	YES	Fuel Type	ELECTRIC
Bottom Element Only (Main Cavity)	YES	Interior Light (Main Cavity)	YES
Bottom Element Only (Upper Cavity)		Interior Light (Upper Cavity)	
Catalytic Liners	NO	Main Cavity Capacity	70
Control Panel Lock	NO	Multifunctional Main Cavity	YES
Control Type	DIAL & TOUCH	Number of Functions (Main Cavity)	9
Defrost Feature (Upper Cavity)		Number of Functions (Upper Cavity)	
Defrost Feature (Main Cavity)	YES	Oven Liner Type	
Display Type	LED	Pre-Fitted Plug/Cable	YES
Door Hinge Position	BOTTOM	Programmable Timer	YES
Double Glazed Glass Door	YES	Pyrolytic Liners	NO
Electrical Connection Required		Second Cavity Capacity	
Energy Consumption Conv. (Main Cavity)	0.99	Single or Double Oven	SINGLE
Energy Consumption Conv. (Second Cavity)		Top and Bottom Element (Main Cavity)	YES
Energy Consumption Fan (Main Cavity)	0.79	Top and Bottom Element (Upper Cavity)	
Energy Consumption Fan (Second Cavity)		Top Element Only (Upper Cavity)	
Fan Assisted Main Oven	YES	Top Element Only (Main Cavity)	NO