

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200659529](#)  
**Status:** **Active**  
**Overview:** Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable  
**Description:** Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 5 Poles, Male (Straight) to Pigtail, 22 AWG, Unshielded WSOR Cable, Grey 5th Wire, 10.0m (32.81') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E152210

**General**

Product Family Industrial Cordsets  
 Series [120065](#)  
 Connector End A Micro-Change (M12)  
 Connector End B Pigtail  
 IP Rating IP67  
 Material - Contact Brass  
 Overview [Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable](#)  
 Product Name Micro-Change (M12)  
 Protocol N/A  
 Region Europe  
 Type Single Ended  
 UPC 889056070829

**Physical**

Cable Diameter 5.50mm (.216")  
 Cable Length 10.0m (32.81')  
 Color - Cable Jacket Black  
 Coupling Style Knurled Hexnut, Threaded  
 Gender Male-Pigtail  
 Keyway Single  
 LED Indicator No  
 Material - Cable Jacket TPU  
 Material - Connector Body TPU  
 Material - Coupling Nut Nickel-plated Brass  
 Material - Plating Mating Gold  
 Orientation Straight to Pigtail  
 Poles 5  
 Temperature Range - Operating -25°C to +85°C  
 Wire Size AWG 22  
 Wire/Cable Type WSOR

**Electrical**

Current - Maximum per Contact 4.0A  
 Voltage - Maximum 60V

**Material Info**

Engineering Number 805006B30M100

**Reference - Drawing Numbers**

Sales Drawing 1200659964-00P, SD-120065-073



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[120065 Series](#)

This document was generated on 04/03/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**