




MIRO TR 90-250VAC FK OPTO-COUPLER MODULE

IN: 250 VAC/DC - OUT: 48 VDC / 0,5 A

Transistor 0.5 A
230 V AC
Spring clamp terminals

[Link to Product](#)**Illustration**

stay connected



Product may differ from Image

Approvals



Input

Voltage range ON	90...250 V AC
Voltage range OFF	0...40 V AC
Control current	7 mA
LED display	LED (yellow)

General data

Test isolation voltage	3.75 kV
Mounting method	DIN-rail mountable (EN 60715)
Housing	Black plastic, flame retardant
Temperature range	-20...+60 °C
Dimensions H x W x D	78x6.2x65 mm

Output

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 05/15

Switching voltage	5...48 V DC
Switching current per output	0.1 mA...0.5 A
Saturation voltage (across output)	max. 1.2 V DC
Leakage current (output is open)	max. 0.3 mA
Switching time ON/OFF	100/700 μ s
Switching frequency	max. 500/30 Hz (resist./ind.)

Commercial data

country of origin	CZ
customs tariff number	85414090
minimum order quantity	1