

DIGITAL MONITORING RELAY SPEED MONITORING
 FROM 0.1 TO 2200 REV/MIN OVERSHOOT AND
 UNDERSHOOT AC/DC 24 TO 240V DC AND AC 50 TO
 60 HZ STARTUP DELAY 1 TO 900S TRIPPING
 DELAYED 0.1 TO 99.9S HYSTERESIS 0.1 TO 99
 REV/MIN 1 CHANGEOVER CONTACT W. OR W/O
 ERROR LOG SPRING-LOADED TYPE

Product function	RPM monitoring relay
-------------------------	----------------------

Measuring circuit:		
Measurable line frequency	Hz	50 ... 60
Adjustable response delay time		
• when starting	s	1 ... 900
• with lower or upper limit violation	s	0.1 ... 99.9
Adjustable response value speed	1/min	0.1 ... 2 200
Input voltage at digital input 1		
• initial value for signal<0>-recognition	V	0
• Full-scale value for signal<0> recognition	V	1
• initial value for signal<1>-recognition	V	4.5
• Full-scale value for signal<1> recognition	V	30
Input current at digital input 2		
• initial value for signal<0>-recognition	mA	0
• Full-scale value for signal<0> recognition	mA	1.2
• initial value for signal<1>-recognition	mA	2.1
• Full-scale value for signal<1> recognition	mA	8.2
Design of input feedback input		No
Design of the sensor		
• at digital input 1 connectable		PNP switching three-wire sensor or mechanical impulse contact with external DC supply (4.5 V ... 30 V)
• at digital input 2 connectable		2-conductor Namur sensor or mechanical impulse contact
Input current at digital input 1 maximum	mA	50
Pulse duration minimum	ms	5
Pulse interval minimum	ms	5
Number of sensor signals per revolution		1 ... 10
Switching hysteresis for rotational speed	1/min	0 ... 99.9

General technical data:		
Design of the display		LCD
Product function		

<ul style="list-style-type: none"> • rotation speed monitoring • Standstill monitoring • Fault storage • External reset • Auto-reset • Manual RESET • Adjustable open/closed-circuit current principle 		Yes
		No
		Yes
		Yes
		Yes
		Yes
		Yes
Startup time after the control supply voltage has been applied	ms	500
Response time maximum	ms	100
Buffering time in the event of power failure minimum	ms	10
Relative metering precision	%	10
Accuracy of digital display		+/- 1 Digit
Relative repeat accuracy	%	1
Type of voltage of the control supply voltage		AC/DC
Control supply voltage		
<ul style="list-style-type: none"> • with AC <ul style="list-style-type: none"> — at 50 Hz Rated value — at 60 Hz Rated value • for DC Rated value 	V	24 ... 240
	V	24 ... 240
	V	24 ... 240
Operating range factor control supply voltage rated value		
<ul style="list-style-type: none"> • with AC <ul style="list-style-type: none"> — at 50 Hz — at 60 Hz • for DC 		1.1 ... 0.8
		1.1 ... 0.8
		0.8 ... 1.1
Surge voltage resistance Rated value	kV	4
Active power consumption	W	2
Protection class IP		IP20
Electromagnetic compatibility		IEC 60947-1 / IEC 61000-6-2 / IEC 61000-6-4
Shock resistance acc. to IEC 60068-2-27		sinusoidal half-wave 15g / 11 ms
Installation altitude at height above sea level maximum	m	2 000
Conducted interference due to burst acc. to IEC 61000-4-4		2 kV
Conducted interference due to conductor-earth surge acc. to IEC 61000-4-5		2 kV
Conducted interference due to conductor-conductor surge acc. to IEC 61000-4-5		1 kV
Electrostatic discharge acc. to IEC 61000-4-2		6 kV contact discharge / 8 kV air discharge
Field-bound parasitic coupling acc. to IEC 61000-4-3		10 V/m
Insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 Rated value	V	300

Degree of pollution		3
Apparent power consumption		
<ul style="list-style-type: none"> • with AC <li style="padding-left: 20px;">— at 24 V maximum <li style="padding-left: 20px;">— at 240 V maximum 	V·A V·A	4 9
Ambient temperature		
<ul style="list-style-type: none"> • during operation • during storage • during transport 	°C °C °C	-25 ... +60 -40 ... +80 -40 ... +80
Galvanic isolation		
<ul style="list-style-type: none"> • between entrance and outlet • between the outputs 		Yes No
Suitability for use safety-related circuits		No
Category acc. to EN 954-1		none
Safety Integrity Level (SIL) acc. to IEC 61508		none

Mechanical data:		
Width	mm	22.5
Height	mm	86
Depth	mm	103
mounting position		any
Required spacing for grounded parts		
<ul style="list-style-type: none"> • forwards • Backwards • at the side • upwards • downwards 	mm mm mm mm mm	0 0 0 0 0
Required spacing with side-by-side mounting		
<ul style="list-style-type: none"> • forwards • Backwards • at the side • upwards • downwards 	mm mm mm mm mm	0 0 0 0 0
Required spacing for live parts		
<ul style="list-style-type: none"> • forwards • Backwards • at the side • upwards • downwards 	mm mm mm mm mm	0 0 0 0 0
Mounting type		screw and snap-on mounting
Product function removable terminal for auxiliary and control circuit		Yes
Type of electrical connection		spring-loaded terminals

Type of connectable conductor cross-section		
<ul style="list-style-type: none"> • solid 		2x (0.25 ... 1.5 mm ²)
<ul style="list-style-type: none"> • finely stranded <ul style="list-style-type: none"> — with core end processing — without core end processing 		2 x (0.25 ... 1.5 mm ²) 2x (0.25 ... 1.5 mm ²)
<ul style="list-style-type: none"> • for AWG conductors <ul style="list-style-type: none"> — solid — stranded 		2x (24 ... 16) 2x (24 ... 16)

Outputs:

Number of NO contacts delayed switching		0
Number of NC contacts delayed switching		0
Number of CO contacts delayed switching		1
Ampacity of the output relay		
<ul style="list-style-type: none"> • at AC-15 <ul style="list-style-type: none"> — at 250 V at 50/60 Hz • at DC-13 <ul style="list-style-type: none"> — at 24 V — at 125 V — at 250 V 	A A A A	3 1 0.2 0.1
Operating current at 17 V minimum	mA	5
Continuous current of the DIAZED fuse link of the output relay	A	4
Mechanical service life (switching cycles) typical		10 000 000
Electrical endurance (switching cycles) at AC-15 at 230 V typical		100 000
Operating frequency with 3RT2 contactor maximum	1/h	5 000

Certificates/ approvals:

General Product Approval	EMC	Test Certificates
---------------------------------	------------	--------------------------



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

Shipping Approval	other
--------------------------	--------------



[Declaration of Conformity](#)

[other](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=3UG46512AW30>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3UG46512AW30>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=3UG46512AW30&lang=en

last modified:

15.01.2015