Connection Line M12 × 1; 8-pin



S88-2MPUR


Part Number




Technical Data

Mechanical Data		
Connection 1	Socket, straight	
Connection mode 1	M12 × 1, 8-pin	
Connection 2	stripped	
Torque	M12: 0,5 Nm	
Cable Length	2 m	
Cable Diameter	6,6 mm	
Wire cross-section	0,25 mm ²	
Degree of Protection	IP67	
Temperature Range	-2580 °C	
Cable Jacket Material	PUR	
Material Wire Insulation	PP	
Material Sleeve Nut	CuZn, nickel-plated	
Screened	yes	
Halogen-free	yes yes	
Drag Chain Suitable		
Bending radius (fixed installation)	> 5 × d	
Bending radius (used in motion)	> 10 × d	
Travel speed (with 5 m horizontal travel distance)	≤ 3,3 m/s	
Acceleration	≤ 5 m/s²	
Bending cycles	> 2000000	
Packaging unit	1 Piece	
Connection Diagram No.	S17	
Connection Equipment No.	88	

- Halogen free, drag chain suitability
- PUR, straight
- Screened







Legen	d		PT	Pla
+	Supply Voltage +		nc	nc
-	Supply Voltage 0 V		U	Te
~	Supply Voltage (AC Voltage)		Ū	Te
A	Switching Output	(NO)	W	Tri
Ā	Switching Output	(NC)	W -	Gr
٧	Contamination/Error Output	(NO)	0	Ar
V	Contamination/Error Output	(NC)	0-	Gr
E	Input (analog or digital)		BZ	B
Т	Teach Input		Amv	Va
Z	Time Delay (activation)		а	Va
S	Shielding		b	Va
RxD	Interface Receive Path		SY	Sy
TxD	Interface Send Path		SY-	Gr
RDY	Ready		E+	Re
GND	Ground		S+	Er
CL	Clock		÷	Gr
E/A	Output/Input programmable		SnR	Sv
0	IO-Link		Rx+/-	- Et
PoE	Power over Ethernet		Tx+/-	- Et
IN	Safety Input		Bus	Int
OSSD	Safety Output		La	Er
Signal	Signal Output		Mag	M
BI_D+/-	Ethernet Gigabit bidirect. data	a line (A-D)	RES	In
EN08542	Encoder 0-pulse 0-0 (TTL)		EDM	Co

	PT	Platinum measuring resistor	ENAR5422	Encoder A/Ā (TTL)	
	пс	not connected	ENBRS422	Encoder B/B (TTL)	
	U	Test Input	ENa	Encoder A	
	Ū	Test Input inverted	ENв	Encoder B	
	W	Trigger Input	Amin	Digital output MIN	
	W -	Ground for the Trigger Input	Амах	Digital output MAX	
	0	Analog Output	Аок	Digital output OK	
	0-	Ground for the Analog Output	SY In	Synchronization In	
	BZ	Block Discharge	SY OUT	Synchronization OUT	
	Anv	Valve Output	Out	Brightness output	
	а	Valve Control Output +	м	Maintenance	
	b	Valve Control Output 0 V	rsv	reserved	
	SY	Synchronization	Wire Co	olors according to DIN IEC 75	
	SY-	Ground for the Synchronization	BK	Black	
	E+	Receiver-Line	BN	Brown	
	S+	Emitter-Line	RD	Red	
	÷	Grounding	OG	Orange	
	SnR	Switching Distance Reduction	YE	Yellow	
	Rx+/-	Ethernet Receive Path	GN	Green	
	Tx+/-	Ethernet Send Path	BU	Blue	
	Bus	Interfaces-Bus A(+)/B(-)	VT	Violet	
	La	Emitted Light disengageable	GY	Grey	
	Mag	Magnet activation	WH	White	
	RES	Input confirmation	PK	Pink	
	EDM	Contactor Monitoring	GNYE	Green/Yellow	

Specifications are subject to change without notice

ling to DIN IEC 757

System Components and Software