


T-Pulleys System MAED-FIX® with Clamp Hub, Pitch 5mm from Aluminium



Material: Aluminium similar to EN AW2017A. Flanges zinc-plated steel. Screw DIN 912-12.9, black.

The hubs of the pulleys are slotted, similar to clamp collars single-split (shaft collars). The pulleys are fixed on the shafts with the clamping screw. No more machining, quick assembly, does not damage the shaft, even distribution of clamping forces.


Ordering Details: e.g.: Product No. 162314K04, Pulley System MAED-FIX, Pitch T5, 14 Teeth, Timing Belt Width 16 mm, Bore 4 mm

Profile T 5, Timing Belt Width 16 mm

| Product No. Belt Width 16 mm | Designation | Number of teeth | Bore B ^{H7} ¹⁾ mm | Type | Outside-Ø Pulley mm | Outside-Ø Flange mm | d mm | ND mm | b mm | L mm | R ²⁾ mm | b ₁ mm | Screw DIN 912 mm | Fastening torque Nm | Transmittable torque ³⁾ Nm | Weight g |
|------------------------------------|----------------|--------------------|---|------|---------------------------|---------------------------|---------|----------|---------|---------|-----------------------|----------------------|------------------------|---------------------------|---|-------------|
| 162 314 K04 | ALK 29 T5/14-2 | 14 | 4 | 1F | 21,44 | 25 | 22,28 | 15 | 21 | 29 | 19,6 | 5,8 | M2,5 x 8 | 1,21 | 1,84 | 24,3 |
| 162 314 K05 | ALK 29 T5/14-2 | 14 | 5 | 1F | 21,44 | 25 | 22,28 | 15 | 21 | 29 | 19,6 | 5,8 | M2,5 x 8 | 1,21 | 2,28 | 23,9 |
| 162 314 K06 | ALK 29 T5/14-2 | 14 | 6 | 1F | 21,44 | 25 | 22,28 | 15 | 21 | 29 | 19,6 | 5,8 | M2,5 x 8 | 1,21 | 2,64 | 23,2 |
| 162 315 K04 | ALK 29 T5/15-2 | 15 | 4 | 1F | 23,03 | 28 | 23,87 | 16 | 21 | 29 | 19,6 | 5,8 | M2,5 x 8 | 1,21 | 1,83 | 28,8 |
| 162 315 K05 | ALK 29 T5/15-2 | 15 | 5 | 1F | 23,03 | 28 | 23,87 | 16 | 21 | 29 | 19,6 | 5,8 | M2,5 x 8 | 1,21 | 1,76 | 28,4 |
| 162 315 K06 | ALK 29 T5/15-2 | 15 | 6 | 1F | 23,03 | 28 | 23,87 | 16 | 21 | 29 | 19,6 | 5,8 | M2,5 x 8 | 1,21 | 2,61 | 27,7 |
| 162 316 K04 | ALK 29 T5/16-2 | 16 | 4 | 1F | 24,62 | 32 | 25,45 | 20 | 21 | 29 | 22,5 | 5,8 | M2,5 x 8 | 1,21 | 1,92 | 35,7 |
| 162 316 K05 | ALK 29 T5/16-2 | 16 | 5 | 1F | 24,62 | 32 | 25,45 | 20 | 21 | 29 | 22,5 | 5,8 | M2,5 x 8 | 1,21 | 2,34 | 35,3 |
| 162 316 K06 | ALK 29 T5/16-2 | 16 | 6 | 1F | 24,62 | 32 | 25,45 | 20 | 21 | 29 | 22,5 | 5,8 | M2,5 x 8 | 1,21 | 2,76 | 34,5 |
| 162 316 K08 | ALK 29 T5/16-2 | 16 | 8 | 1F | 24,62 | 32 | 25,45 | 20 | 21 | 29 | 22,5 | 5,8 | M2,5 x 8 | 1,21 | 3,54 | 32,9 |
| 162 318 K04 | ALK 29 T5/18-2 | 18 | 4 | 1F | 27,81 | 32 | 28,65 | 20 | 21 | 29 | 22,5 | 5,8 | M2,5 x 8 | 1,21 | 1,92 | 42,0 |
| 162 318 K05 | ALK 29 T5/18-2 | 18 | 5 | 1F | 27,81 | 32 | 28,65 | 20 | 21 | 29 | 22,5 | 5,8 | M2,5 x 8 | 1,21 | 2,34 | 43,0 |
| 162 318 K06 | ALK 29 T5/18-2 | 18 | 6 | 1F | 27,81 | 32 | 28,65 | 20 | 21 | 29 | 22,5 | 5,8 | M2,5 x 8 | 1,21 | 2,76 | 41,0 |
| 162 318 K08 | ALK 29 T5/18-2 | 18 | 8 | 1F | 27,81 | 32 | 28,65 | 20 | 21 | 29 | 22,5 | 5,8 | M2,5 x 8 | 1,21 | 3,54 | 39,2 |
| 162 319 K04 | ALK 31 T5/19-2 | 19 | 4 | 1F | 29,40 | 36 | 30,24 | 24 | 21 | 31 | 27,0 | 7,3 | M3 x 10 | 2,1 | 3,29 | 52,6 |
| 162 319 K05 | ALK 31 T5/19-2 | 19 | 5 | 1F | 29,40 | 36 | 30,24 | 24 | 21 | 31 | 27,0 | 7,3 | M3 x 10 | 2,1 | 4,01 | 52,1 |
| 162 319 K06 | ALK 31 T5/19-2 | 19 | 6 | 1F | 29,40 | 36 | 30,24 | 24 | 21 | 31 | 27,0 | 7,3 | M3 x 10 | 2,1 | 4,75 | 51,6 |
| 162 319 K08 | ALK 31 T5/19-2 | 19 | 8 | 1F | 29,40 | 36 | 30,24 | 24 | 21 | 31 | 27,0 | 7,3 | M3 x 10 | 2,1 | 6,12 | 49,6 |
| 162 319 K10 | ALK 31 T5/19-2 | 19 | 10 | 1F | 29,40 | 36 | 30,24 | 24 | 21 | 31 | 27,0 | 7,3 | M3 x 10 | 2,1 | 7,42 | 47,4 |
| 162 320 K04 | ALK 31 T5/20-2 | 20 | 4 | 1F | 30,99 | 36 | 31,83 | 24 | 21 | 31 | 27,0 | 7,3 | M3 x 10 | 2,1 | 3,29 | 56,3 |
| 162 320 K05 | ALK 31 T5/20-2 | 20 | 5 | 1F | 30,99 | 36 | 31,83 | 24 | 21 | 31 | 27,0 | 7,3 | M3 x 10 | 2,1 | 4,01 | 55,7 |
| 162 320 K06 | ALK 31 T5/20-2 | 20 | 6 | 1F | 30,99 | 36 | 31,83 | 24 | 21 | 31 | 27,0 | 7,3 | M3 x 10 | 2,1 | 4,75 | 55,2 |
| 162 320 K08 | ALK 31 T5/20-2 | 20 | 8 | 1F | 30,99 | 36 | 31,83 | 24 | 21 | 31 | 27,0 | 7,3 | M3 x 10 | 2,1 | 6,12 | 53,3 |
| 162 320 K10 | ALK 31 T5/20-2 | 20 | 10 | 1F | 30,99 | 36 | 31,83 | 24 | 21 | 31 | 27,0 | 7,3 | M3 x 10 | 2,1 | 7,42 | 51,0 |
| 162 322 K04 | ALK 31 T5/22-2 | 22 | 4 | 1F | 34,17 | 38 | 35,01 | 27 | 21 | 31 | 29,1 | 7,3 | M3 x 10 | 2,1 | 3,33 | 65,4 |
| 162 322 K05 | ALK 31 T5/22-2 | 22 | 5 | 1F | 34,17 | 38 | 35,01 | 27 | 21 | 31 | 29,1 | 7,3 | M3 x 10 | 2,1 | 4,12 | 64,9 |
| 162 322 K06 | ALK 31 T5/22-2 | 22 | 6 | 1F | 34,17 | 38 | 35,01 | 27 | 21 | 31 | 29,1 | 7,3 | M3 x 10 | 2,1 | 4,82 | 64,4 |
| 162 322 K08 | ALK 31 T5/22-2 | 22 | 8 | 1F | 34,17 | 38 | 35,01 | 27 | 21 | 31 | 29,1 | 7,3 | M3 x 10 | 2,1 | 6,24 | 62,5 |
| 162 322 K10 | ALK 31 T5/22-2 | 22 | 10 | 1F | 34,17 | 38 | 35,01 | 27 | 21 | 31 | 29,1 | 7,3 | M3 x 10 | 2,1 | 7,58 | 60,2 |
| 162 322 K12 | ALK 31 T5/22-2 | 22 | 12 | 1F | 34,17 | 38 | 35,01 | 27 | 21 | 31 | 29,1 | 7,3 | M3 x 10 | 2,1 | 8,85 | 57,5 |
| 162 324 K05 | ALK 31 T5/24-2 | 24 | 5 | 1F | 37,36 | 42 | 38,20 | 28 | 21 | 31 | 29,1 | 7,3 | M3 x 10 | 2,1 | 4,02 | 76,9 |
| 162 324 K06 | ALK 31 T5/24-2 | 24 | 6 | 1F | 37,36 | 42 | 38,20 | 28 | 21 | 31 | 29,1 | 7,3 | M3 x 10 | 2,1 | 4,79 | 76,3 |
| 162 324 K08 | ALK 31 T5/24-2 | 24 | 8 | 1F | 37,36 | 42 | 38,20 | 28 | 21 | 31 | 29,1 | 7,3 | M3 x 10 | 2,1 | 6,20 | 74,4 |
| 162 324 K10 | ALK 31 T5/24-2 | 24 | 10 | 1F | 37,36 | 42 | 38,20 | 28 | 21 | 31 | 29,1 | 7,3 | M3 x 10 | 2,1 | 7,54 | 72,2 |
| 162 324 K12 | ALK 31 T5/24-2 | 24 | 12 | 1F | 37,36 | 42 | 38,20 | 28 | 21 | 31 | 29,1 | 7,3 | M3 x 10 | 2,1 | 8,82 | 69,4 |
| 162 325 K06 | ALK 34 T5/25-2 | 25 | 6 | 1F | 38,95 | 44 | 39,79 | 32 | 21 | 34 | 35,4 | 10,0 | M4 x 12 | 4,6 | 8,13 | 93,2 |
| 162 325 K08 | ALK 34 T5/25-2 | 25 | 8 | 1F | 38,95 | 44 | 39,79 | 32 | 21 | 34 | 35,4 | 10,0 | M4 x 12 | 4,6 | 10,5 | 91,2 |
| 162 325 K10 | ALK 34 T5/25-2 | 25 | 10 | 1F | 38,95 | 44 | 39,79 | 32 | 21 | 34 | 35,4 | 10,0 | M4 x 12 | 4,6 | 12,9 | 88,8 |
| 162 325 K12 | ALK 34 T5/25-2 | 25 | 12 | 1F | 38,95 | 44 | 39,79 | 32 | 21 | 34 | 35,4 | 10,0 | M4 x 12 | 4,6 | 15,0 | 85,7 |
| 162 325 K14 | ALK 34 T5/25-2 | 25 | 14 | 1F | 38,95 | 44 | 39,79 | 32 | 21 | 34 | 35,4 | 10,0 | M4 x 12 | 4,6 | 17,1 | 82,2 |
| 162 326 K08 | ALK 34 T5/26-2 | 26 | 8 | 1F | 40,54 | 44 | 41,38 | 32 | 21 | 34 | 35,4 | 10,0 | M4 x 12 | 4,6 | 10,5 | 95,9 |
| 162 326 K10 | ALK 34 T5/26-2 | 26 | 10 | 1F | 40,54 | 44 | 41,38 | 32 | 21 | 34 | 35,4 | 10,0 | M4 x 12 | 4,6 | 12,9 | 93,5 |
| 162 326 K12 | ALK 34 T5/26-2 | 26 | 12 | 1F | 40,54 | 44 | 41,38 | 32 | 21 | 34 | 35,4 | 10,0 | M4 x 12 | 4,6 | 15,0 | 90,5 |
| 162 326 K14 | ALK 34 T5/26-2 | 26 | 14 | 1F | 40,54 | 44 | 41,38 | 32 | 21 | 34 | 35,4 | 10,0 | M4 x 12 | 4,6 | 17,1 | 86,9 |
| 162 327 K08 | ALK 34 T5/27-2 | 27 | 8 | 1F | 42,13 | 48 | 42,97 | 34 | 21 | 34 | 37,4 | 10,0 | M4 x 12 | 4,6 | 10,7 | 107 |
| 162 327 K10 | ALK 34 T5/27-2 | 27 | 10 | 1F | 42,13 | 48 | 42,97 | 34 | 21 | 34 | 37,4 | 10,0 | M4 x 12 | 4,6 | 13,1 | 104 |
| 162 327 K12 | ALK 34 T5/27-2 | 27 | 12 | 1F | 42,13 | 48 | 42,97 | 34 | 21 | 34 | 37,4 | 10,0 | M4 x 12 | 4,6 | 15,4 | 101 |
| 162 327 K14 | ALK 34 T5/27-2 | 27 | 14 | 1F | 42,13 | 48 | 42,97 | 34 | 21 | 34 | 37,4 | 10,0 | M4 x 12 | 4,6 | 17,5 | 97,7 |
| 162 327 K15 | ALK 34 T5/27-2 | 27 | 15 | 1F | 42,13 | 48 | 42,97 | 34 | 21 | 34 | 37,4 | 10,0 | M4 x 12 | 4,6 | 18,5 | 95,7 |
| 162 327 K16 | ALK 34 T5/27-2 | 27 | 16 | 1F | 42,13 | 48 | 42,97 | 34 | 21 | 34 | 37,4 | 10,0 | M4 x 12 | 4,6 | 19,7 | 93,5 |

¹⁾ Bore tolerance in wheel area H7 continuous; in clamping area H7 before slotting. ²⁾ Interference circle-Ø screw head. ³⁾ Max. friction torque of the hub.

T-Pulleys System MAED-FIX® with Clamp Hub, Pitch 5mm from Aluminium



Material: Aluminium similar to EN AW2017A. Flanges zinc-plated steel. Screw DIN 912-12.9, black.

The hubs of the pulleys are slotted, similar to clamp collars single-split (shaft collars). The pulleys are fixed on the shafts with the clamping screw. No more machining, quick assembly, does not damage the shaft, even distribution of clamping forces.

Ordering Details: e.g.: Product No. 162328K08, Pulley System MAED-FIX, Pitch T5, 28 Teeth, Timing Belt Width 16 mm, Bore 8 mm

Profile T 5, Timing Belt Width 16 mm

| Product No. Belt Width 16 mm | Designation | Number of teeth | Bore B ^{H7} ¹⁾ mm | Type | Outside-Ø Pulley mm | Outside-Ø Flange mm | d mm | ND mm | b mm | L mm | R ²⁾ mm | b ₁ mm | Screw DIN 912 mm | Fastening torque Nm | Transmittable torque ³⁾ Nm | Weight g |
|------------------------------------|----------------|--------------------|---|------|---------------------------|---------------------------|---------|----------|---------|---------|-----------------------|----------------------|------------------------|---------------------------|---|-------------|
| 162 328 K08 | ALK 34 T5/28-2 | 28 | 8 | 1F | 43,72 | 48 | 44,56 | 34 | 21 | 34 | 37,4 | 10 | M4 x 12 | 4,6 | 10,7 | 112 |
| 162 328 K10 | ALK 34 T5/28-2 | 28 | 10 | 1F | 43,72 | 48 | 44,56 | 34 | 21 | 34 | 37,4 | 10 | M4 x 12 | 4,6 | 13,1 | 109 |
| 162 328 K12 | ALK 34 T5/28-2 | 28 | 12 | 1F | 43,72 | 48 | 44,56 | 34 | 21 | 34 | 37,4 | 10 | M4 x 12 | 4,6 | 15,4 | 106 |
| 162 328 K14 | ALK 34 T5/28-2 | 28 | 14 | 1F | 43,72 | 48 | 44,56 | 34 | 21 | 34 | 37,4 | 10 | M4 x 12 | 4,6 | 17,5 | 103 |
| 162 328 K15 | ALK 34 T5/28-2 | 28 | 15 | 1F | 43,72 | 48 | 44,56 | 34 | 21 | 34 | 37,4 | 10 | M4 x 12 | 4,6 | 18,5 | 101 |
| 162 328 K16 | ALK 34 T5/28-2 | 28 | 16 | 1F | 43,72 | 48 | 44,56 | 34 | 21 | 34 | 37,4 | 10 | M4 x 12 | 4,6 | 19,7 | 99 |
| 162 330 K08 | ALK 34 T5/30-2 | 30 | 8 | 1F | 46,91 | 51 | 47,75 | 39 | 21 | 34 | 41,4 | 10 | M4 x 12 | 4,4 | 10,5 | 134 |
| 162 330 K10 | ALK 34 T5/30-2 | 30 | 10 | 1F | 46,91 | 51 | 47,75 | 39 | 21 | 34 | 41,4 | 10 | M4 x 12 | 4,4 | 12,9 | 131 |
| 162 330 K12 | ALK 34 T5/30-2 | 30 | 12 | 1F | 46,91 | 51 | 47,75 | 39 | 21 | 34 | 41,4 | 10 | M4 x 12 | 4,4 | 15,1 | 128 |
| 162 330 K14 | ALK 34 T5/30-2 | 30 | 14 | 1F | 46,91 | 51 | 47,75 | 39 | 21 | 34 | 41,4 | 10 | M4 x 12 | 4,4 | 17,3 | 125 |
| 162 330 K15 | ALK 34 T5/30-2 | 30 | 15 | 1F | 46,91 | 51 | 47,75 | 39 | 21 | 34 | 41,4 | 10 | M4 x 12 | 4,4 | 18,5 | 123 |
| 162 330 K16 | ALK 34 T5/30-2 | 30 | 16 | 1F | 46,91 | 51 | 47,75 | 39 | 21 | 34 | 41,4 | 10 | M4 x 12 | 4,4 | 19,4 | 120 |
| 162 330 K20 | ALK 34 T5/30-2 | 30 | 20 | 1F | 46,91 | 51 | 47,75 | 39 | 21 | 34 | 41,4 | 10 | M4 x 12 | 4,4 | 23,3 | 111 |
| 162 332 K10 | ALK 34 T5/32-2 | 32 | 10 | 1F | 50,09 | 54 | 50,93 | 42 | 21 | 34 | 43 | 10 | M4 x 12 | 4,2 | 12,2 | 151 |
| 162 332 K12 | ALK 34 T5/32-2 | 32 | 12 | 1F | 50,09 | 54 | 50,93 | 42 | 21 | 34 | 43 | 10 | M4 x 12 | 4,2 | 14,4 | 148 |
| 162 332 K14 | ALK 34 T5/32-2 | 32 | 14 | 1F | 50,09 | 54 | 50,93 | 42 | 21 | 34 | 43 | 10 | M4 x 12 | 4,2 | 16,5 | 144 |
| 162 332 K15 | ALK 34 T5/32-2 | 32 | 15 | 1F | 50,09 | 54 | 50,93 | 42 | 21 | 34 | 43 | 10 | M4 x 12 | 4,2 | 17,5 | 142 |
| 162 332 K16 | ALK 34 T5/32-2 | 32 | 16 | 1F | 50,09 | 54 | 50,93 | 42 | 21 | 34 | 43 | 10 | M4 x 12 | 4,2 | 18,5 | 140 |
| 162 332 K20 | ALK 34 T5/32-2 | 32 | 20 | 1F | 50,09 | 54 | 50,93 | 42 | 21 | 34 | 43 | 10 | M4 x 12 | 4,2 | 22,3 | 130 |
| 162 336 K10 | ALK 34 T5/36-2 | 36 | 10 | 1F | 56,46 | 63 | 57,30 | 42 | 21 | 34 | 43 | 10 | M4 x 12 | 4,2 | 12,2 | 186 |
| 162 336 K12 | ALK 34 T5/36-2 | 36 | 12 | 1F | 56,46 | 63 | 57,30 | 42 | 21 | 34 | 43 | 10 | M4 x 12 | 4,2 | 14,4 | 183 |
| 162 336 K14 | ALK 34 T5/36-2 | 36 | 14 | 1F | 56,46 | 63 | 57,30 | 42 | 21 | 34 | 43 | 10 | M4 x 12 | 4,2 | 16,5 | 179 |
| 162 336 K15 | ALK 34 T5/36-2 | 36 | 15 | 1F | 56,46 | 63 | 57,30 | 42 | 21 | 34 | 43 | 10 | M4 x 12 | 4,2 | 17,5 | 177 |
| 162 336 K16 | ALK 34 T5/36-2 | 36 | 16 | 1F | 56,46 | 63 | 57,30 | 42 | 21 | 34 | 43 | 10 | M4 x 12 | 4,2 | 18,5 | 175 |
| 162 336 K20 | ALK 34 T5/36-2 | 36 | 20 | 1F | 56,46 | 63 | 57,30 | 42 | 21 | 34 | 43 | 10 | M4 x 12 | 4,2 | 22,3 | 165 |
| 162 336 K25 | ALK 34 T5/36-2 | 36 | 25 | 1F | 56,46 | 63 | 57,30 | 42 | 21 | 34 | 43 | 10 | M4 x 12 | 4,2 | 26,9 | 150 |
| 162 340 K12 | ALK 38 T5/40-2 | 40 | 12 | 1F | 62,82 | 66 | 63,66 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 23,6 | 253 |
| 162 340 K14 | ALK 38 T5/40-2 | 40 | 14 | 1F | 62,82 | 66 | 63,66 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 27,1 | 249 |
| 162 340 K15 | ALK 38 T5/40-2 | 40 | 15 | 1F | 62,82 | 66 | 63,66 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 28,7 | 247 |
| 162 340 K16 | ALK 38 T5/40-2 | 40 | 16 | 1F | 62,82 | 66 | 63,66 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 30,4 | 244 |
| 162 340 K20 | ALK 38 T5/40-2 | 40 | 20 | 1F | 62,82 | 66 | 63,66 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 36,9 | 233 |
| 162 340 K25 | ALK 38 T5/40-2 | 40 | 25 | 1F | 62,82 | 66 | 63,66 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 44,4 | 216 |
| 162 342 K12 | ALK 38 T5/42-2 | 42 | 12 | 1F | 66,01 | 71 | 66,85 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 23,6 | 274 |
| 162 342 K14 | ALK 38 T5/42-2 | 42 | 14 | 1F | 66,01 | 71 | 66,85 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 27,1 | 270 |
| 162 342 K15 | ALK 38 T5/42-2 | 42 | 15 | 1F | 66,01 | 71 | 66,85 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 28,7 | 268 |
| 162 342 K16 | ALK 38 T5/42-2 | 42 | 16 | 1F | 66,01 | 71 | 66,85 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 30,4 | 265 |
| 162 342 K20 | ALK 38 T5/42-2 | 42 | 20 | 1F | 66,01 | 71 | 66,85 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 36,9 | 254 |
| 162 342 K25 | ALK 38 T5/42-2 | 42 | 25 | 1F | 66,01 | 71 | 66,85 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 44,4 | 237 |
| 162 348 K12 | ALK 38 T5/48-0 | 48 | 12 | 2 | 75,55 | - | 76,39 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 23,6 | 313 |
| 162 348 K14 | ALK 38 T5/48-0 | 48 | 14 | 2 | 75,55 | - | 76,39 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 27,1 | 309 |
| 162 348 K15 | ALK 38 T5/48-0 | 48 | 15 | 2 | 75,55 | - | 76,39 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 28,7 | 307 |
| 162 348 K16 | ALK 38 T5/48-0 | 48 | 16 | 2 | 75,55 | - | 76,39 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 30,4 | 305 |
| 162 348 K20 | ALK 38 T5/48-0 | 48 | 20 | 2 | 75,55 | - | 76,39 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 36,9 | 294 |
| 162 348 K25 | ALK 38 T5/48-0 | 48 | 25 | 2 | 75,55 | - | 76,39 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 44,4 | 276 |
| 162 360 K12 | ALK 38 T5/60-0 | 60 | 12 | 2 | 94,65 | - | 95,49 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 23,6 | 454 |
| 162 360 K14 | ALK 38 T5/60-0 | 60 | 14 | 2 | 94,65 | - | 95,49 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 27,1 | 450 |
| 162 360 K15 | ALK 38 T5/60-0 | 60 | 15 | 2 | 94,65 | - | 95,49 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 28,7 | 448 |
| 162 360 K16 | ALK 38 T5/60-0 | 60 | 16 | 2 | 94,65 | - | 95,49 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 30,4 | 445 |
| 162 360 K20 | ALK 38 T5/60-0 | 60 | 20 | 2 | 94,65 | - | 95,49 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 36,9 | 434 |
| 162 360 K25 | ALK 38 T5/60-0 | 60 | 25 | 2 | 94,65 | - | 95,49 | 50 | 21 | 38 | 54,2 | 13,5 | M5 x 20 | 8 | 44,4 | 417 |

¹⁾ Bore tolerance in wheel area H7 continuous; in clamping area H7 before slotting. ²⁾ Interference circle-Ø screw head. ³⁾ Max. friction torque of the hub.