
	<b>TECHNICAL DATA SHEET</b>	code	<b>URM70</b>
		version	<b>2</b>
		date	<b>2007-10-25</b>
	<b>COAX Uniradio No. M70</b>	page	<b>1/2</b>

## APPLICATION

Coaxial communication cable based on BS2316.

## CONSTRUCTION




1	Inner conductor	Stranded tinned copper
2	Dielectric	Solid PE
3	Braid	Bare copper
4	Sheath	PVC according the European Standard HD 624.

## REQUIREMENTS AND TEST METHODS

Test methods in accordance with European standard EN 50289.

### Mechanical characteristics

1. Inner conductor:		7 x 0.2 mm
Diameter:		0.6 mm ± 0.02 mm
2. Dielectric:		
Diameter:		3.25 mm ± 0.15 mm
3. Outer conductor:		
Diameter screen:		3.93 mm ± 0.2 mm
Coverage braid:		91 % ± 4 %
4. Sheath:		
Diameter:		5.8 mm ± 0.25 mm
Tensile strength:		≥ 12.5 N/mm <sup>2</sup>
Elongation at break:		≥ 150 %
5. Cable:		
Crush resistance of cable:		< 1% (load of 700N)
Storage/operating temperature:		-40°C to +70°C
Minimum installation temperature:		-5 °C
Minimum static bend radius:		30 mm

	<b>TECHNICAL DATA SHEET</b>	code	<b>URM70</b>
		version	<b>2</b>
		date	<b>2007-10-25</b>
	<b>COAX Uniradio No. M70</b>	page	<b>2/2</b>

**Electrical characteristics**

Mean characteristic impedance:	$75 \pm 3 \Omega$
Regularity of impedance:	$> 40 \text{ dB}$
DC resistance inner conductor:	$\leq 92 \Omega/\text{km}$
Capacitance:	$67 \text{ pF/m} \pm 2 \text{ pF/m}$
Nominal velocity of propagation:	$66 \%$
Insulation resistance:	$> 2 \cdot 10^4 \text{ M}\Omega \cdot \text{km}$
Voltage Rating	
DC:	3.6 kVdc
RMS	1.8 kVrms

Return loss at	5-30 MHz:	$\geq 20 \text{ dB}^*$
	30-470 MHz:	$\geq 20 \text{ dB}^*$
	470-1000 MHz:	$\geq 18 \text{ dB}^*$

\*Max. 3 peak values 4 dB lower than specified.

Nominal Attenuation:

100 MHz:	15.2 dB/100m
200 MHz:	21.8 dB/100m
600 MHz:	39.1 dB/100m
1000 MHz:	51.7 dB/100m



Belden CDT believes this product to be in compliance with the environmental regulations EU RoHS (Directive 2002/95/EC, 27 January 2003); this is valid for all material produced after the RoHS compliant date for this product.