

Product information

99 10 300

High Leverage Concreters' Nipper

High lever transmission

DIN ISO 9242



- 25 % less effort required compared to conventional concreters' nippers of the same size
- Extra-slim form for tying deep mounted steel rods
- To lace concrete reinforcing steel with binding wire from a roll
- Wire is twisted and cut in a single pass
- High-leverage joint, minimising strain, even when thick binding wires are used
- The high damping of the cutting stroke on cutting through the binding wire reduces the strain on tendons and muscles
- Cutting edges additionally hardened; cutting edge hardness approx. 61 HRC
- High-grade special tool steel, forged, multi stage oil-hardened



General

| | |
|-----------------|-----------------------|
| Article No. | 99 10 300 |
| EAN | 4003773022398 |
| Pliers | black atramentized |
| Head | polished |
| Weight | 501 g |
| Dimensions | 300 x 50 x 20 mm |
| Standard | DIN ISO 9242 |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

Technical details

| | |
|--|-----------------|
| Cutting capacities hard wire (diameter) | Ø 2.0 mm |
| Cutting capacities medium hard wire (diameter) | Ø 3.8 mm |
| Cutting edge length mm | 25.0 mm 25.0 mm |

technical change and errors excepted

