

Product Summary

BV _{DSS}	Rds(on)	I _D T _C = +25°С	
	57mΩ @ V _{GS} = 10V	20A	
100V	71mΩ @ Vgs = 6V	18A	
	96mΩ @ V _{GS} = 4.5V	16A	

Description and Applications

This new generation N-Channel Enhancement Mode MOSFET is designed to minimize RDS(ON) yet maintain superior switching performance. This device is ideal for use in notebook battery power management and load switch.

PowerDI5060-8 (SWP) (Type UX)

- **DC-DC Converters**
- Load Switch

Features

- Rated to +175°C Ideal for High Ambient Temperature Environments
- 100% Unclamped Inductive Switching Ensures More Reliable and Robust End Application
- High Conversion Efficiency .
- Low RDS(ON) Minimizes On State Losses
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts gualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/


Mechanical Data

- Case: PowerDI[®]5060-8
- Case Material: Molded Plastic. "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections: See Diagram Below
- Terminals: Finish Matte Tin Annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.097 grams (Approximate)



Top View

Bottom View



Ordering Information (Note 4)

Part Number	Case	Packaging
DMTH10H072LPS-13	PowerDI5060-8 (SWP) (Type UX)	2,500 / Tape & Reel


1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied. Notes:

2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



) | | = Manufacturer's Marking TH1H72LS = Product Type Marking Code YYWW = Date Code Marking YY or \overline{YY} = Year (ex: 21 = 2021) WW = Week (01 to 53)

PowerDI is a registered trademark of Diodes Incorporated.



Maximum Ratings (@Tc = +25°C, unless otherwise specified.)

Characteristic			Symbol	Value	Unit
Drain-Source Voltage			Vdss	100	V
Gate-Source Voltage			V _{GSS}	±20	V
Continuous Drain Current, V _{GS} = 10V (Note 7)	Steady State	Tc = +25°C Tc = +100°C	lD	20 14	А
Maximum Continuous Body Diode Forward Current (Note 7)			ls	20	A
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%)			Ідм	80	A
Pulsed Body Diode Forward Current (10µs Pulse, Duty Cycle = 1%)			lsм	80	A
Avalanche Current, L = 0.1mH (Note 8)			las	6	А
Avalanche Energy, L = 0.1mH (Note 8)			E _{AS}	1.8	mJ

Thermal Characteristics (@Tc = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 5)	T _A = +25°C	PD	1.5	W
Thermal Resistance, Junction to Ambient (Note 5)	Steady State	RθJA	98	°C/W
Total Power Dissipation (Note 6)	T _A = +25°C	PD	3.0	W
Thermal Resistance, Junction to Ambient (Note 6)	Steady State	R _{θJA}	49	°C/W
Total Power Dissipation (Note 7)	Tc = +25°C	PD	51.7	W
Thermal Resistance, Junction to Case (Note 7)		R ₀ JC	2.9	°C/W
Operating and Storage Temperature Range		T _{J,} T _{STG}	-55 to +175	°C

Electrical Characteristics (@Tc = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 9)	eyniser		• 76	max	Unit		
Drain-Source Breakdown Voltage	BVDSS	100	_	—	V	$V_{GS} = 0V, I_D = 250 \mu A$	
Zero Gate Voltage Drain Current	IDSS	_	—	1	μA	$V_{DS} = 80V, V_{GS} = 0V$	
Gate-Source Leakage	Igss			±100	nA	$V_{GS} = \pm 20V, V_{DS} = 0V$	
ON CHARACTERISTICS (Note 9)				•		·	
Gate Threshold Voltage	V _{GS(TH)}	1	_	3	V	$V_{DS} = V_{GS}$, $I_D = 250 \mu A$	
		_	44	57	mΩ	Vgs = 10V, ID = 4.5A	
Static Drain-Source On-Resistance	R _{DS(ON)}	_	54	71		$V_{GS} = 6V, I_D = 4A$	
		_	73	96		V _{GS} = 4.5V, I _D = 2.6A	
Diode Forward Voltage	Vsd	_	0.7	1.2	V	VGS = 0V, IS = 1A	
DYNAMIC CHARACTERISTICS (Note 10)						·	
Input Capacitance	Ciss		266	_		$V_{DS} = 50V, V_{GS} = 0V,$ f = 1MHz	
Output Capacitance	Coss	_	87.2	—	pF		
Reverse Transfer Capacitance	Crss	_	3.6	_			
Gate Resistance	Rg	_	7.0	—	Ω	$V_{DS} = 0V, V_{GS} = 0V, f = 1MHz$	
Total Gate Charge (V _{GS} = 4.5V)	Qg	_	2.8	—		V _{DS} = 50V, I _D = 4.5A	
Total Gate Charge (V _{GS} = 10V)	Qg	_	5.1	—	nC		
Gate-Source Charge	Q _{gs}	_	0.8	_	nc		
Gate-Drain Charge	Q _{gd}	_	1.7	—			
Turn-On Delay Time	tD(ON)	_	3.0	_			
Turn-On Rise Time	tR		2.8	_		$\label{eq:VDD} \begin{split} V_{DD} &= 50 V, \ V_{GS} = 10 V, \\ I_D &= 4.5 A, \ R_G = 3 \Omega \end{split}$	
Turn-Off Delay Time	tD(OFF)	_	9.5	—	ns		
Turn-Off Fall Time	tF	_	3.2	—			
Body Diode Reverse Recovery Time	trr		37.5	_	ns		
Body Diode Reverse Recovery Charge	Q _{RR}		86.8	_	nC	– I _S = 4.5A, di/dt = 300A/μs	

Notes: 5. Device mounted on FR-4 PC board, with minimum recommended pad layout, single sided.


6. Device mounted on FR-4 substrate PC board, 2oz copper, with thermal bias to bottom layer 1inch square copper plate.

7. Thermal resistance from junction to soldering point (on the exposed drain pad).

8. I_{AS} and E_{AS} ratings are based on low frequency and duty cycles to keep $T_J = +25^{\circ}C$. 9. Short duration pulse test used to minimize self-heating effect. 10. Guaranteed by design. Not subject to product testing.




DMTH10H072LPS



DMTH10H072LPS Document number: DS39699 Rev. 3 - 2




DMTH10H072LPS



DMTH10H072LPS Document number: DS39699 Rev. 3 - 2







PowerDI5060-8 (SWP)

(Type UX)

Max

1.10

0.05

0.50

0.35

0.25REF

5.15 BSC

3.96

4.18

3.86

1.27BSC

--

0.200 0.400 0.300

0.050REF

0.025 0.225 0.125

4.005

12°

8°

6.40 BS

0.230 0.330

4.70 5.10

5.60 6.00

4.195 4.595

0.635 0.835

0.635 0.835

All Dimensions in mm

Тур

1.00

0.41

0.25

0.277

4.90

3.76

3.98

5.80

3.66

4.395

0.735

0.735

3.605

11°

7°

Min

0.90

0

0.30

0.20

3.56

3.78

3.46

1.05

3.205

10°

6°

Dim

Α

A1

b

b2

b4

c D

D1

D2

D2a

Ε

E1

E2

E2a

е

k

L

La L1

L1a

L4


Μ

θ

θ1

Package Outline Dimensions


Please see http://www.diodes.com/package-outlines.html for the latest version.



PowerDI5060-8 (SWP) (Type UX)

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.



PowerDI5060-8 (SWP) (Type UX)

Dimensions	Value (in mm)		
С	1.270		
G	0.660		
G1	0.820		
Х	0.610		
X1	4.100 4.420		
X2			
Y	1.270		
Y1	1.020		
Y2	3.810		
Y3	6.610		



IMPORTANT NOTICE

1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5. products provided subject to Diodes' Standard Terms and Conditions of Sale Diodes are (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2021 Diodes Incorporated

www.diodes.com