

Bore plug gauge OD

Version for blind holes



Application:

For quick comparison measurements of bores during series inspections.
The slightly undersized, ground sleeve is used to guide and centre the plug gauge in the bore.

Execution:

- Cemented carbide measuring contacts and measuring needles (wear-resistant)
- Plug gauge from dia. 130 mm can be supplied as a cross-shaped sleeves or cross-shaped sleeves with skids
- Version for blind holes with reduced face size

Advantage:

- Easy to use
- Minimum measuring times
- Maximum measuring accuracy
- Robust and reliable
- Adapted to the desired bore diameter and tolerance



Art. no.	33566 160
Brand	SCHWENK
Manufacturer Part Number	31300501
Design of measuring contact	Carbide
Min./max. diameter of measuring range	150.1-160 mm
Measurement travel	0.2 mm
Front size	1.2 mm
Repeat accuracy	2 µm
Sleeve length	55 mm
Connection thread	M11 x 0.75
Gross Weight	2.200 kg
Product Group	334