

## Electric caterpillar stair climber CT070B ERGO

Load capacity 105 kg

**DMS**<sup>®</sup>  
ARBEIT WIRD LEICHTER

### Application:

The electric caterpillar stair climber is ideal for transporting all kinds of goods through open terrain and stairways.

### Execution:

- This stair climber features rubber tracks, which enable it to move through spiral staircases and narrow stair platforms
- It's easy to make slight corrections to the direction
- Its speed of up to 35 steps/min and its weight of only 18.5 kg allow fast transport of items weighing up to 105 kg
- Climbing speed: 25-35 steps/min
- Dimension/handrail folded: 215 x 505 x 1030 mm
- Toe plate size: 470 x 240 mm
- Wheels: 152 mm
- Battery: Lithium-ion, 48 V 5 Ah
- Motor: 200 W

### Advantage:

- The self-braking crawler gearbox makes transporting items over stairs safe
- Low-impact transport via all types of stairways
- Fast - up to 35 steps/min.



<b>Art. no.</b>	<b>50191 101</b>
<b>Brand</b>	DMS
<b>Manufacturer Part Number</b>	CT105
<b>Height</b>	1430 mm
<b>Toe plate width</b>	470 mm
<b>Toe plate depth</b>	240 mm
<b>Load-carrying capacity</b>	105 kg
<b>Width</b>	505 mm
<b>Depth</b>	455 mm
<b>Wheel diameter</b>	152 mm
<b>Gross Weight</b>	24.000 kg
<b>Product Group</b>	586

### EAN

4260625310250