

## Manual forklift, manual hydraulic forklift truck

Carrying capacity 500 and 1000 kg

**fetra**  
Transportgeräte

### Application:

for occasional use as a lifting and transport device

### Execution:

- Stable section steel construction
- with tubular push handles
- Hydraulic pump with chrome-plated piston and overload valve actuation via drawbar
- Lowering valve via hand lever
- Load centre distance: 585 mm
- 2 castors, polyurethane tyre wheels 150 x 40 mm and 2 polyurethane fork rollers 80 x 70 mm. Castors with locking device.

<b>Art. no.</b>	<b>50262 503</b>
<b>Brand</b>	FETRA
<b>Manufacturer Part Number</b>	6855
<b>Load-carrying capacity</b>	500 kg
<b>Length</b>	1600 mm
<b>Width</b>	794 mm
<b>Fork length</b>	1150 mm
<b>Fork arm width</b>	160 mm
<b>Fork, external distance</b>	540 mm
<b>Fork roller diameter</b>	80 mm
<b>Min. lift height</b>	88 mm
<b>Lift height</b>	1500 mm
<b>Material of wheel</b>	Polyurethane
<b>Total stop optional</b>	No
<b>Gross Weight</b>	210.000 kg
<b>Height</b>	2010 mm
<b>Wheel diameter</b>	150 mm
<b>Wheel width</b>	40 mm
<b>Product Group</b>	5AE



### EAN

4017976068558