

Pneumatic angle deburring tool BEW 605

To countersink dia. 24 mm



Application:

For countersinking and deburring of bores in poorly accessible places.

Execution:

- Rear air exhaust
- With speed control

Advantage:

- For deburring larger holes

Delivery:

Includes collet chuck, 6 mm. Collet chuck key and hose unit, in box



| | |
|-----------------------------------|------------------|
| Art. no. | 78253 010 |
| Brand | BIAX DRUCKLUFT |
| Manufacturer Part Number | 1508 10930 |
| Model | BEW 605 |
| Valve design | Lever valve |
| Max. idle speed | 500 rpm |
| Air consumption | 300 l/min |
| Max. clamping diameter | 6 mm |
| Min./max. idle speed | 0-500 rpm |
| Suitable for bore diameter | 24 mm |
| Inner hose diameter | 7 mm |
| Length | 352.5 mm |
| Head height | 25 mm |
| Diameter of housing | 35 mm |
| Weight | 0.82 kg |
| Sound-pressure level | 71 dB |
| Gross Weight | 1.625 kg |
| Product Group | 748 |