Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: ESYLUX

Supplier's address: -

Model identifier: EL10810848 A

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	DLS			
Light source cap-type	230V AC 50Hz					
(or other electric interface)						
Mains or non-mains:	MLS	Connected light source (CLS):	Nein			
Colour-tuneable light source:	Nein	Envelope:	-			
High luminance light source:	Nein					
Anti-glare shield:	Nein	Dimmable:	No			
Product parameters						

Parameter		Value	Parameter	Value			
General product parameters:							
• ·	nption in on- 00 h), rounded st integer	30	Energy efficiency class	F			
indicating if it re in a sphere (30	us flux (фuse), efers to the flux 50º), in a wide n a narrow cone	- in -	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	_			
On-mode p expressed in W	oower (P _{on}),	-	Standby power (P _{sb}), expressed in W and rounded to the second decimal	-			
	dby power (P _{net}) ssed in W and second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI- values that can be set				
Outer dimensions without	Height Width Depth	-	Spectral power distribution in the	See image in last page			
	Deptii	-					

separate control gear, lighting control parts and non- lighting control parts, if any (millimetre)		range 250 nm to 800 nm, at full-load				
Claim of equivalent power ^(a)	-	If yes, equivalent power (W)	-			
		Chromaticity coordinates (x and y)				
Parameters for directional light sources:						
Peak luminous intensity (cd)	_	Beam angle in degrees, or the range of beam angles that can be set				
Parameters for LED and OLED lig	ht sources:					
R9 colour rendering index value	-	Survival factor	-			
the lumen maintenance factor	-					
Parameters for LED and OLED ma	ains light sources:					
displacement factor (cos φ1)	0,94	Colour consistency in McAdam ellipses	-			
Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage.	_(b)	lf yes then replacement claim (W)	-			
Flicker metric (Pst LM)	-	Stroboscopic effect metric (SVM)	-			

(a)_{'-'} : not applicable;

(b)'-' : not applicable;