

Tilting container with roll-off mechanism—favourable load centre

Carrying capacity 1000 kg, without wheels

Application:

For the collection and disposal of all types of bulk goods and solid materials.

Version:

- Tilting at any height using a wire rope from the stacker seat
- Sheet metal tray with surrounding edge profile
- Sturdy base frame with fork pockets
- Protection against accidental slipping and tipping
- All dimensions without wheels

Advantage:

- With roll-off mechanism
- Favourable load centre

Delivery:

Goods supplied without packaging as standard. Packaging available for an additional charge.



Art. no.	50266 560
Volume	0.5 m ³
Length	1420 mm
Width	1008 mm
Tipper edge height	1070 mm
Height	1070 mm
Fork pocket clearance	600 mm
Fork pocket size (W x H)	200 x 91 mm
With drain valve	No
With stacker seat tilt function	Yes
With perforated sheet	No
Load-carrying capacity	1000 kg
Surface	Zinc plated

EAN-Code

4052462019775