

# Safety isolating transformer VB 2,8/1/15



Picture shows VB 2,0/2/6

## Advantages


Minimum size at high output
Inherently short-circuit proof
Also with dual output voltage for series or parallel connection
Designed for high ambient temperatures
Permanent corrosion protection, high insulation value and maximum electrical reliability thanks to XtraDenseFill resin encapsulation
Self-extinguishing potting material

## Applications

As a mains transformer for adjustment of the voltage and simple electrical isolation.

As a safety isolating transformer for the safe electrical isolation of the input and output sides. The transformer is suitable for creating SELV and PELV circuits because of the limit on the output voltage.

## Sample application



## Standards

Safety isolating transformer  
to: VDE 0570 Part 2-6, DIN EN 61558-2-6, EN 61558-2-6, IEC 61558-2-6,  
UL 5085-1/-2, CSA 22.2 No.66

## Approvals



VDE, UL 5085-1/-2, CSA 22.2 No.66




# Safety isolating transformer

## VB 2,8/1/15

Type		VB 2,8/1/15
Electrical data	Input	
	Rated input voltage	230 Vac
	Rated frequency	50 - 60 Hz
	Output	
	Rated output voltage	15 Vac
	Rated Power	2.8 VA
	No-load voltage (app. x factor)	1.80
	No-load loss (typ.)	1.40 W
	Efficiency	57.0 %
	Standards	
	Classification	Safety isolating transformer
	Approvals	
	Approvals	cURus, VDE
	Environment	
	Ambient temperature max.	70 °C
Safety and protection		
Type	Encapsulated	
Insulation class	VDE=B, UL=class 105	
Protection index	IP 00	
Safety class (prepared)	II	
Short circuit strength	inherently short-circuit proof	
Order numbers		
<b>Order Number</b>	<b>VB 2,8/1/15</b>	

Type		VB 2,8/1/15
Terminal and mounting	Terminals	Pins for printed circuit boards
Measures and weights	Pin (ø)	0.8 mm
	Core type	EI 30/23,0
	Weight	0.14 kg



Subject to change.