Solenoid/pneumatic valves, Tiger Classic





Solenoid/pneumatic valves, Tiger Classic

FESTO

Key features

General information

- Highly durable poppet valve concept for all 3/2 and 5/2-way valves
- Pneumatic or electrical actuation with F solenoid coil
- With flow rates of up to 7500 l/min
- Pipe thread in sizes G1/8, G1/4, G1/2 and G3/4
- Tried and tested assembly on PAL or PRS manifold strips with hollow holts
- Optimised response times with patented U-ring and servo control





Solenoid coils

F solenoid coils

Voltage:

- 12 to 230 V DC
- 12 to 240 V AC (50 to 60 Hz)

Power consumption:

• 4.5 W

- Selected types acc. to ATEX directive for explosive atmospheres
- Easily interchangeable solenoid coils
- Solenoid coil not included in scope of delivery

Variants

VL/0-3-...

Depending upon selected connections:

Normally closed or normally open

MFH-3-..., MOFH-3-...

• MFH-3-... Normally closed

• MOFH-3-... Normally open These valves can be converted from one function to the other by rotating the seal under the cover.

MFH-3-...-S

This valve type can be used within a range of 0 to 8 bar and also as MOFH (through flow when not actuated) with a separate pilot line.

MFH-5-...-S

The external pilot air connection means that these valves can also be used with low operating pressures.

Solenoid/pneumatic valves, Tiger Classic



Key features

Manifold mounting

With PAL manifold strip



With PRS manifold block




The Tiger Classic valves can be mounted on PAL manifold strips with common supply port or on PRS manifold blocks with common supply port and common exhausts. The valves are mounted on the strips and blocks with hollow bolts.

The manifold strip and manifold block have 2 to 6 valve positions.

Vacant positions can be sealed on PAL manifold strips with blanking caps, or with blanking plates on PRS manifold blocks.

Separate pressure levels can be provided to individual valves by means of hollow bolts with threaded connection.



Solenoid valves, Tiger Classic Product range overview



Function	Design	Туре	Pneumatic connection	Operating voltage		
				[V DC]	[V AC]	
3/2-way	Solenoid valve	-	<u>'</u>	<u>'</u>		
valves		MFH	G1/8	12, 24, 42, 48	24, 42, 48, 110, 230, 240	
			G1/4			
			G1/2			
			G3/4			
		MOFH	G1/8	12, 24, 42, 48	24, 42, 48, 110, 230, 240	
			G1/4			
	101		G1/2			
			G3/4			

Function	Design	Туре	Pneumatic connection	Operating voltage	Operating voltage						
				[V DC]	[V AC]						
5/2-way	Solenoid valve										
valves		MFH	G1/8	12, 24, 42, 48	24, 42, 48, 110, 230, 240						
	100		G1/4								
	مودون المحادث		G1/2								
				<u> </u>							
	Double solenoid valve										
		JMFH	G1/8	12, 24, 42, 48	24, 42, 48, 110, 230, 240						
			G1/4								
			G1/2								
	0 000		"		<u> </u>						
		<u>'</u>									
	Double solenoid	valve with don	ninant signal								
		JMFDH	G1/8	12, 24, 42, 48	24, 42, 48, 110, 230, 240						
			G1/4								
					1						
	10 100										

Solenoid valves, Tiger Classic Product range overview



Туре	Normal position		Pilot air supply		Type of reset		→ Page/Internet
	Closed	Open	Internal	External	Air spring	Mechanical spring	
Solenoid valve							
MFH		-			-		12
		-			-		
		-			-		
		-			-		
MOFH	-			-	-		12
	-			-	-		
	_			_	_		
	_			_	_		

Туре	Pilot air supply		Type of reset	Type of reset		
	Internal	External	Air spring	Mechanical spring	→ Page/Interne	
Solenoid va	lve					
MFH			-		17	
			-			
			-			
Double sole	enoid valve					
JMFH	•		-	-	22	
			-	-		
			-	-		
	enoid valve with dominant sigr	ıaı				
		_	_	_	22	
Double sole JMFDH	-					


Pneumatic valves, Tiger Classic Product range overview



Function	Design	Туре	Pneumatic connection	Type of reset	→ Page/Internet						
				Air spring	Mechanical spring						
3/2-way valves	Pneumatic valve										
		VL/O	G1/8	-		29					
			G1/4	-							
			G1/2	-							
			G3/4	-							
					-						
5/2-way valves	Pneumatic valve										
	100	VL	G1/8	-		33					
		000	G1/4	-							
			G1/2	-							
	Double pilot valve		_								
		JH	G1/8	-	-	36					
			G1/4	-	-						
			G1/2	-	_						
	Davida allaticale		4 -11								
	Double pilot valve					24					
		JDH	G1/8		-	36					
	000		G1/4		-						


Solenoid valves, Tiger Classic Type codes








Mounting on manifold block









Accessories		
	Brief description	→ Page/Internet
1 Push-in fitting	For connecting standard O.D. tubing	quick star
QS		
2 Blanking plug	3 included in the scope of delivery for PRS manifold block	blanking plug
В		
3 Manifold block		42
PRS		
4 Silencer	For fitting in exhaust ports	u
5 Hollow bolt	For distribution of compressed air or for separate compressed air supply	41
VT		
6 Solenoid valve	For F solenoid coil	4
MFH		
7 Double solenoid valve	For F solenoid coil	4
JMFH		
8 F solenoid coil		msfg, msfw
MSFG, MSFW		
9 Luminescent seal	For displaying the switching status	44
MLD		
10 Blanking plate	For covering an unused valve position	43
PRSB		
11 Plug socket	For valves MFH, JMFH	44
MSSD-F		
12 Plug socket with cable	For valves MFH, JMFH	44
KMF		
13 Plug socket	For valves MFH, JMFH	44
MSSD-F-S		



Mounting on manifold strip







Accessories		
	Brief description	→ Page/Internet
1 Push-in fitting	For connecting standard O.D. tubing	quick star
QS		
2 Blanking plug	1 included in the scope of delivery for PAL manifold strip	blanking plug
В		
3 Manifold strip		40
PAL		
4 Silencer	For fitting in exhaust ports	u
5 Hollow bolt	For distribution of compressed air or for separate compressed air supply	41
VT	Tot distribution of compressed an orior separate compressed an supply	41
6 Solenoid valve	For F solenoid coil	4
MFH		
7 Double solenoid valve	For F solenoid coil	4
JMFH		
8 F solenoid coil		msfg, msfw
MSFG, MSFW		
9 Luminescent seal	For displaying the switching status	44
MLD		
10 Blanking cap	For blanking an unused valve position	41
VTM		
11 Plug socket	For valves MFH, JMFH	44
MSSD-F		
12 Plug socket with cable	For valves MFH, JMFH	44
KMF		
13 Plug socket	For valves MFH, JMFH	44
MSSD-F-S		



- N - Flow rate 500 ... 7500 l/min Wearing parts kits → 16



12

Voltage 12, 24, 42, 48 V DC 24, 42, 48, 110, 230, 240 V AC




General technical data						
Pneumatic connection		G1/8	G1/4	G1/2	G3/4	
Valve function		3/2-way, single sol	enoid			
Constructional design		Poppet valve				
Sealing principle		Soft				
Actuation type		Electrical				
Type of reset		Mechanical spring				
Type of control		Piloted				
Pilot air supply		Internal or external				
Direction of flow		Non reversible (reversible for external pilot air supply)				
Exhaust function		With flow control				
Manual override		Detenting				
Type of mounting		Via through holes				
Mounting position		Any				
Nominal size	[mm]	5	7	14	19	
Standard nominal flow rate	[l/min]	500	800	3700	7500	
Product weight	[g]	240	320	1100	1260	

Operating and environmental cond	litions					
Pneumatic connection			G1/8	G1/4	G1/2	G3/4
Operating medium			Compressed air in ac	cordance with ISO 85	73-1:2010 [7:4:4]	
Note on operating/pilot medium			Operation with lubric	ated medium possibl	e (in which case lubrica	ated operation will
			always be required)			
Operating pressure	Internal pilot air supply	[bar]	1.5 8			2 8
	External pilot air supply	[bar]	-0.95 +10			
Pilot pressure		[bar]	1 8			
Ambient temperature		[°C]	-5 +40			
Temperature of medium		[°C]	-10 +60			
Note on materials			RoHS-compliant			
Certification			c CSA us (OL)		-	
			c UL us - Recognized	(HL)	-	




Minimal pilot pressure p12/p14 as a function of operating pressure p1 (external pilot air supply)


MFH-3-1/8-S








MFH-3-1/2-S



MFH-3-3/4-S




Valve response times [ms]								
Pneumatic connection	G1/8		G1/4		G1/2		G3/4	
Normal position	Closed	Open	Closed	Open	Closed	Open	Closed	Open
Internal pilot air supply								
On	9	9	10	15	18	18	40	40
Off	29	29	29	45	90	90	29	29
External pilot air supply								
On	9	_	10	_	18	-	40	-
Off	29	_	29	_	90	_	29	-



Electrical data			
F solenoid coil			
Electrical connection			Plug vanes for plug sockets MSSD-F, KMF
Operating voltage	D.C. voltage	[V DC]	12, 24, 42, 48
	A.C. voltage	[V AC]	24, 42, 48, 110, 230, 240 (50 60 Hz)
Coil characteristics	D.C. voltage	[W]	4.5
	A.C. voltage	[VA]	Pull: 7.5
			Hold: 6
Protection class to EN 60 529			IP65 (in combination with plug socket)

Materials

Sectional view





1	Housing	Aluminium die-cast, anodised
-	Seals	Nitrile rubber

Solenoid valves MFH, Tiger Classic

FESTO

Technical data – 3/2-way valves







Ordering data				
Circuit symbol	Description	Pneumatic connection	Part No.	Туре
12 2	Without F solenoid coil ¹⁾ ,	G1/8	7802	MFH-3-1/8
	internal pilot air supply	G1/4	9964	MFH-3-1/4
		G1/2	9857	MFH-3-1/2
82 1 3		G3/4	11967	MFH-3-3/4
	,		1	
110 2	Without F solenoid coil ¹⁾ ,	G1/8	7877	MOFH-3-1/8
	internal pilot air supply	G1/4	7876	MOFH-3-1/4
		G1/2	7884	MOFH-3-1/2
82 11 33		G3/4	11969	MOFH-3-3/4
12 2	Without F solenoid coil ¹⁾ ,	G1/8	7958	MFH-3-1/8-S
	external pilot air supply	G1/4	7959	MFH-3-1/4-S
		G1/2	7960	MFH-3-1/2-S
12 82 1 3		G3/4	11968	MFH-3-3/4-S

¹⁾ F solenoid coils → 44

Ordering data – Wearing parts kits						
Pneumatic connection	Part No.	Туре				
G1/8	104206	MFH-3-1/8				
G1/4	104207	MFH-3-1/4				
G1/2	104208	MFH-3-1/2				

FESTO

- N - Flow rate

500 ... 3700 l/min

Wearing parts kits → 21

- **4** - Voltage 12, 24, 42, 48 V DC 24, 42, 48, 110, 230, 240 V AC




General technical data						
Pneumatic connection		G1/8	G1/4	G1/2		
Valve function		5/2-way, single s	olenoid			
Constructional design		Poppet valve				
Sealing principle		Soft				
Actuation type		Electrical				
Type of reset		Mechanical spring				
Type of control		Piloted				
Direction of flow		Non reversible (reversible for external pilot air supply)				
Pilot air supply		Internal or external				
Exhaust function		With flow control				
Manual override		Detenting				
Type of mounting		Via through holes				
Mounting position		Any				
Nominal size	[mm]	5	7	14		
Standard nominal flow rate	[l/min]	500	1000	3700		
Product weight	[g]	270	290	1135		

Operating and environmental cond	itions				
Pneumatic connection			G1/8	G1/4	G1/2
Operating medium			Compressed air in accordan	ce with ISO 8573-1:2010 [7:4	:4]
Note on operating/pilot medium			Operation with lubricated medium possible (in which case lubricated operation will always be required)		
Operating pressure	Internal pilot air supply	[bar]	1.8 8	2.2 8	2 8
	External pilot air supply	[bar]	0 10	0 8	0 8
Pilot pressure		[bar]	1 8	1.5 8	1.5 8
Ambient temperature [°C]			-5 +40		
Temperature of medium [°C]			-10 +60		
Note on materials			RoHS-compliant		




Minimal pilot pressure p12, p14 as a function of operating pressure p1 (external pilot air supply)

MFH-5-1/8-S




----- Exhaust throttled Exhaust unthrottled MFH-5-1/4-S



---- Exhaust throttled - Exhaust unthrottled

MFH-5-1/2-S



----- Exhaust throttled Exhaust unthrottled


Valve response times [ms]						
Pneumatic connection	G1/8		G1/4		G1/2	
Pilot air supply	Internal	External	Internal	External	Internal	External
On	8	8	9	9	15	21
Off	36	36	29	29	154	150



Electrical data			
F solenoid coil			
Electrical connection			Plug vanes for plug sockets MSSD-F, KMF
Operating voltage	D.C. voltage	[V DC]	12, 24, 42, 48
	A.C. voltage	[V AC]	24, 42, 48, 110, 230, 240 (50 60 Hz)
Coil characteristics	D.C. voltage	[W]	4.5
	A.C. voltage	[VA]	Pull: 7.5
			Hold: 6
Protection class to EN 60529			IP65 (in combination with plug socket)

Materials

Sectional view





1	Housing	Aluminium die-cast, anodised
-	Seals	Nitrile rubber

Solenoid valves MFH, Tiger Classic



Technical data – 5/2-way valves







Ordering data				
Circuit symbol	Description	Pneumatic connection	Part No.	Туре
14 4 2	Without F solenoid coil 1),	G1/8	9982	MFH-5-1/8
14 4 2	internal pilot air supply	G1/4	6211	MFH-5-1/4
7 / _T W		G1/2	6420	MFH-5-1/2
84 5 1 3				
14 4 2	Without F solenoid coil ¹⁾ ,	G1/8	10348	MFH-5-1/8-S
	external pilot air supply	G1/4	10349	MFH-5-1/4-S
7 / _T W		G1/2	35547	MFH-5-1/2-S
14 84 5 1 3			,	

1) F solenoid coils → 44

Ordering data – Wearing parts kits						
Pneumatic connection	Part No.	Туре				
G1/8	104209	MFH-5-1/8 ¹⁾²⁾				
G1/4	104211	MFH-5-1/4 ³⁾⁴⁾				

- Order mounting sleeves 228389 separately
 Use up to E602 series
 Order mounting sleeves 229363 separately
 Use from 1/81 series



- N - Flow rate 600 ... 4500 l/min Wearing parts kits → 26

Voltage 12, 24, 42, 48 V DC 24, 42, 48, 110, 230, 240 V AC




General technical data						
Pneumatic connection			G1/8	G1/4	G1/2	
Valve function			5/2-way, double solenoid			
Constructional design			Poppet valve			
Sealing principle			Soft			
Actuation type			Electrical			
Type of control			Piloted			
Pilot air supply			Internal or external			
Direction of flow			Non reversible (reversible for external pilot air supply)			
Exhaust function			With flow control			
Manual override			Detenting			
Type of mounting			Via through holes			
Mounting position			Any			
Nominal size		[mm]	5	7	14	
Standard nominal flow rate	Internal pilot air supply	[l/min]	600	1100	4500	
	External pilot air supply	[l/min]	600	1100	4000	
Product weight		[g]	425	530	1210	

Operating and environmental cond	litions				
Pneumatic connection			G1/8	G1/4	G1/2
Operating medium			Compressed air in accordan	ce with ISO 8573-1:2010 [7:4	4:4]
Note on operating/pilot medium			Operation with lubricated m	nedium possible (in which cas	e lubricated operation will
			always be required)		
Operating pressure	Internal pilot air supply	[bar]	1.5 8	1.5 8	2 8
	External pilot air supply	[bar]	0 8	0 8	0 8
	With dominant signal	[bar]	2.5 8	2.5 8	-
Pilot pressure		[bar]	1.2 8	1.2 8	0.5 8
Ambient temperature		[°C]	-5 +40		
Temperature of medium [°C]			-10 +60		
Note on materials			RoHS-compliant		




Minimal pilot pressure p12, p14 as a function of operating pressure p1 (external pilot air supply)

JMFH-5-1/8-S




----- Exhaust throttled Exhaust unthrottled JMFH-5-1/4-S



----- Exhaust throttled Exhaust unthrottled

JMFH-5-1/2-S




Valve response times [ms]					
Pneumatic connection	G1/8		G1/4		G1/2
		Dominating signal at		Dominating signal at	
		14		14	
Internal pilot air supply					
On/changeover	-	16	-	24	-
Off/changeover	18	24	11	32	20
External pilot air supply					
On/changeover	-	-	-	-	-
Off/changeover	18	_	11		20



Electrical data			
F solenoid coil			
Electrical connection			Plug vanes for plug sockets MSSD-F, KMF
Operating voltage	D.C. voltage	[V DC]	12, 24, 42, 48
	A.C. voltage	[V AC]	24, 42, 48, 110, 230, 240 (50 60 Hz)
Coil characteristics	D.C. voltage	[W]	4.5
	A.C. voltage	[VA]	Pull: 7.5
			Hold: 6
Protection class to EN 60529			IP65 (in combination with plug socket)

Materials

Sectional view





1	Housing	Aluminium die-cast, anodised
-	Seals	Nitrile rubber

Double solenoid valves JMFH, Tiger Classic



Technical data – 5/2-way double solenoid valves







Ordering data Circuit symbol	Description	Pneumatic connection	Part No.	Туре
14 4 2 12 12 12 12 12 13 84 5 1 3 82	Without F solenoid coil ¹⁾ , internal pilot air supply	G1/8 G1/4 G1/2	8820 10410 10166	JMFH-5-1/8 JMFH-5-1/4 JMFH-5-1/2
14 4 2 12	Without F solenoid coil ¹⁾ , external pilot air supply	G1/8	14008	JMFH-5-1/8-S
14 84 5 1 3 12		G1/4	14009	JMFH-5-1/4-S
82		G1/2	35548	JMFH-5-1/2-S
14 4 2 12	Without F solenoid coil ¹⁾ , internal pilot air supply, with dominating signal at 14	G1/8	8821	JMFDH-5-1/8
14 84 5 1 3 ₈₂ 12		G1/4	10411	JMFDH-5-1/4


¹⁾ F solenoid coils → 44

Ordering data – Wearing parts kits				
Pneumatic connection	Part No.	Туре		
G1/8	104891	JMFH-5-1/8 ¹⁾		
G1/4	104892	JMFH-5-1/4 ²⁾		

Order mounting sleeves 228389 separately
 Order mounting sleeves 229363 separately

Pneumatic valves, Tiger Classic Type codes






Pneumatic valves, Tiger Classic Peripherals overview







Acce	essories		
		Brief description	→ Page/Internet
1	Push-in fitting	For connecting standard O.D. tubing	quick star
	QS		
2	Blanking plug	3 included in the scope of delivery for PRS manifold block	blanking plug
	В	1 included in the scope of delivery for PAL manifold strip	
3	Manifold block		42
	PRS		
4	Manifold strip		40
	PAL		
5	Silencer	For fitting in exhaust ports	u
6	Pneumatic valve		vl, jh
	VL, JH		
7	Blanking plate	For covering an unused valve position	43
	PRSB		
8	Blanking cap	For blanking an unused valve position	41
	VTM		
9	Hollow bolt	For distribution of compressed air or for separate compressed air supply	41
	VT		

Pneumatic valves VL/O, Tiger Classic Technical data – 3/2-way valves



- 1 - Flow rate 500 ... 7500 l/min

Wearing parts kits → 32



General technical data						
Pneumatic connection		G1/8	G1/4	G1/2	G3/4	
Valve function		3/2-way, single pilot				
Constructional design		Poppet valve				
Sealing principle		Soft				
Actuation type		Pneumatic				
Type of reset		Mechanical spring				
Type of pilot control		Direct				
Direction of flow		Reversible				
Exhaust function		With flow control				
Manual override		None				
Type of mounting		Via through holes				
Mounting position		Any				
Nominal size	[mm]	5	7	14	19	
Standard nominal flow rate	[l/min]	500	800	3700	7500	
Product weight	[g]	150	230	860	1200	

Operating and environment	tal conditions							
Pneumatic connection			G1/8	G1/4	G1/2	G3/4		
Operating medium			Compressed air in	accordance with ISO	8573-1:2010 [7:4:4]			
Note on operating/pilot medium			Operation with lul	Operation with lubricated medium possible (in which case lubricated operation will				
			always be required)					
Operating pressure	Normally closed	[bar]	-0.95 +10	-0.95 +10	-0.95 +10	-0.95 +10		
	Normally open	[bar]	0 10	0 10	0 10	0 10		
Pilot pressure			See diagram (max. 10 bar)					
Ambient temperature [°C]			-10 +60					
Note on materials			RoHS-compliant RoHS-compliant					


Pneumatic valves VL/O, Tiger Classic



Technical data – 3/2-way valves


Minimal pilot pressure p12/p14 as a function of operating pressure p1

VL/0-3-1/8-B




- 1 Switch-on pressure
- 3 Only for normally closed
- 2 Switch-off pressure

VL/O-3-1/4 - Normally closed




- 1 Switch-on pressure
- 2 Switch-off pressure

VL/O-3-1/2 - Normally closed




- 1 Switch-on pressure
- 2 Switch-off pressure

VL/O-3-1/4 - Normally open



- 1 Switch-on pressure
- 2 Switch-off pressure

VL/O-3-1/2 - Normally open




- 1 Switch-on pressure
- 2 Switch-off pressure

Pneumatic valves VL/O, Tiger Classic Technical data – 3/2-way valves




VL/O-3-3/4 - Normally closed



---- Exhaust throttled Exhaust unthrottled

VL/O-3-3/4 - Normally open




---- Exhaust throttled Exhaust unthrottled

Valve response times [ms]					
Pneumatic connection	G1/8	G1/4	G1/2	G3/4	
On	4	8	17	8	
Off	10	30	30	23	

Materials


Sectional view




[1	Housing	Aluminium die-cast, anodised
-	Seals	Nitrile rubber

Pneumatic valves VL/O, Tiger Classic Technical data – 3/2-way valves





Pneumatic connection	B1	B5	D3	H8	H9	L1
G1/8	26	3	G1/8	65	8	45
G1/4	30.4	-	G1/8	80	8	50
G1/2	52	-	G1/4	118	10	80
G3/4	68	_	G1/4	138	10	92



Ordering data				
Circuit symbol	Description	Pneumatic connection	Part No.	Туре
12 2	Mechanical reset,	G1/8	7803	VL/0-3-1/8-B
(110) 	optionally normally open or	G1/4	9984	VL/0-3-1/4
1 - 1 - 1 - 1 - 1 - 1 - 1 - 1 - 1 - 1 -	closed	G1/2	9983	VL/0-3-1/2
		G3/4	10049	VL/0-3-3/4
1(33) 3(11)				

Ordering data – Wearing parts kits				
Pneumatic connection	Part No.	Туре		
G1/8	104222	VL/0-3-1/8-B		
G1/4	104207	VL/0-3-1/4		
G1/2	104208	VL/0-3-1/2		

Pneumatic valves VL, Tiger Classic Technical data – 5/2-way valves



- 1 - Flow rate 500 ... 3700 l/min

Wearing parts kits → 35




General technical data					
Pneumatic connection		G1/8	G1/4	G1/2	
Valve function		5/2-way, single pilot			
Constructional design		Poppet valve			
Sealing principle		Soft			
Actuation type		Pneumatic			
Type of reset	Mechanical spring				
Type of pilot control	Direct				
Direction of flow		Non reversible			
Manual override		None			
Exhaust function		With flow control			
Type of mounting		Via through holes			
Mounting position	Any				
Nominal size	[mm]	5	7	14	
Standard nominal flow rate	[l/min]	500	800	3700	
Product weight	[g]	180	220	1070	

Operating and environmental conditions					
Pneumatic connection		G1/8	G1/4	G1/2	
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]				
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will				
	always be required)				
Operating pressure	[bar]	0 10	0 8	0 10	
Pilot pressure	[bar]	See diagram (max. 10 bar)			
Ambient temperature	[°C]	-10 +60			
Note on materials		RoHS-compliant			


Pneumatic valves VL, Tiger Classic Technical data – 5/2-way valves




Minimal pilot pressure p12/p14 as a function of operating pressure p1



----- Exhaust throttled Exhaust unthrottled




VL-5-1/2



Valve response times [ms]						
Pneumatic connection	G1/8	G1/4	G1/2			
On	5	8	6			
Off	16	12	27			

Materials


Sectional view




1	Housing	Aluminium die-cast, anodised
-	Seals	Nitrile rubber

Pneumatic valves VL, Tiger Classic Technical data – 5/2-way valves

FESTO



Pneumatic connection	B1	B5	D3	Н8	Н9	L1
G1/8	26	3	G1/8	85	8	45
G1/4	30.4	_	G1/8	96	8	50
G1/2	52	-	G1/4	159	10	80




atic connection Part No. Type
71
9764 VL-5-1/8
9199 VL-5-1/4
9445 VL-5-1/2

Ordering data – Wearing parts ki	its	
Pneumatic connection	Part No.	Туре
G1/8	104209	VL-5-1/8 ¹⁾
G1/4	104211	VL-5-1/4 ²⁾³⁾
G1/2	104212	VL-5-1/2

- Order mounting sleeves 228389 separately
 Order mounting sleeves 229363 separately
 Use from 1/81 series





Wearing parts kits → 39




General technical data					
Pneumatic connection	G1/8	G1/4	G1/2		
Valve function		5/2-way, double pilot			
Constructional design		Poppet valve			
Sealing principle		Soft			
Actuation type		Pneumatic			
Type of pilot control	Direct				
Direction of flow		Non reversible			
Exhaust function		With flow control			
Manual override		Resetting			
Type of mounting		Via through holes			
Mounting position		Any			
Nominal size	[mm]	5	7	14	
Standard nominal flow rate	[l/min]	600	1100	4500	
Product weight	[g]	245	330	1130	

Operating and environmental conditions				
Pneumatic connection		G1/8	G1/4	G1/2
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]			
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will			
	always be required)			
Operating pressure	[bar]	0 10	0 8	0 10
Pilot pressure	[bar]	See diagram (max. 10 bar)		
Ambient temperature	[°C]	-10 +60		
Note on materials		RoHS-compliant		




Minimal pilot pressure p12/p14 as a function of operating pressure p1

JH-5-1/8




----- Exhaust throttled Exhaust unthrottled JDH-5-1/8




----- Exhaust throttled Exhaust unthrottled

JH-5-1/4




----- Exhaust throttled - Exhaust unthrottled JDH-5-1/4



Exhaust throttled Exhaust unthrottled

JH-5-1/2




Valve response times [ms]							
Pneumatic connection	G1/8		G1/4	G1/2			
	Dominating signal at		Dominating signal at				
		14		14			
On/changeover	-	9	-	7	-		
Off/changeover	2	16	7	16	3		




Materials

Sectional view




Ī	1 Housing	Aluminium die-cast, anodised
	– Seals	Nitrile rubber



Pneumatic connection	B1	B5	D3	D4 Ø	Н8	Н9	H10	L1
G1/8	26	3	G1/8	5	120	8	132	45
G1/4	30.4	-	G1/8	5	138	8	149	50
G1/2	52	-	G1/4	9.9	178	10	193	80





Ordering data				
Circuit symbol	Description	Pneumatic connection	Part No.	Туре
4. 0. 🗆		G1/8	8823	JH-5-1/8
4 2 7		G1/4	10408	JH-5-1/4
14 12		G1/2	10165	JH-5-1/2
5 1 3				
4 0 🖽	With dominating signal at 14	G1/8	8824	JDH-5-1/8
14 2 7 12		G1/4	10409	JDH-5-1/4
5 1 3				

Ordering data – Wearing parts kits									
Pneumatic connection	Part No.	Туре							
G1/8	104891	JH-5-1/8 ¹⁾							
G1/4	104892	JH-5-1/4 ²⁾							

- Order mounting sleeves 228389 separately
 Order mounting sleeves 229363 separately

Solenoid/pneumatic valves, Tiger Classic Accessories


FESTO

Manifold strip PAL

Materials:

Manifold: Anodised aluminium Mounting bracket: Galvanised steel





Dimensions	Dimensions and ordering data																
Туре	B1	B2	В3	B4	B5	D1	D3	D4	H1	H2	Н3	L5	L6	L7	L8	=©1	=© 2
PAL-1/8	20	21	2	33.5	44.5	G1/8	G1/4	5.2	44	32	43	18	34	12	4	19	8
PAL-1/4	28	27	2	42	56	G1/4	G3/8	7	56	44	56	20	32	14	4	24	10
PAL-1/2	40	40	3	73	93	G1/2	G3/4	11	80	60	75	35	69	16	5	36	17

Number of valve ports	L1	L2	L3	L4	Weight [g]	Part No.	Туре
Pneumatic connecti	on G1/8	1		J.		U.	
2	70	96	114	89	145	8601	PAL-1/8-2
3	104	130	148	123	170	8602	PAL-1/8-3
4	138	164	182	157	190	8603	PAL-1/8-4
5	172	198	216	191	215	8604	PAL-1/8-5
6	206	232	250	225	240	9767	PAL-1/8-6
Pneumatic connecti	on G1/4 ¹⁾						
2	72	100	120	94	330	9188	PAL-5-1/4-2
3	104	132	152	126	405	9189	PAL-5-1/4-3
4	136	164	184	158	480	9190	PAL-5-1/4-4
5	168	196	216	190	555	9191	PAL-5-1/4-5
6	200	228	248	222	630	9192	PAL-5-1/4-6
		1	11	1		,	
Pneumatic connecti	on G1/2						
2	139	181	213	164	770	9492	PAL-1/2-2
3	208	250	282	233	915	9493	PAL-1/2-3
4	277	319	351	302	1060	9494	PAL-1/2-4
5	346	388	420	371	1220	9495	PAL-1/2-5
6	415	457	489	440	1370	9496	PAL-1/2-6

¹⁾ MOFH-3-1/4 is not suitable for manifold mounting

Solenoid/pneumatic valves, Tiger Classic Accessories

FESTO

Hollow bolt

VT

For manifold strip PAL

Material:

Anodised aluminium



Ordering data			
Pneumatic connection	Weight	Part No.	Туре
	[g]		
G1/8	6	8626	VT-1/8
G1/8	15	5928	VT-1/8-1 ¹⁾²⁾
G1/4	15	206147	VT-1/4-2
G1/2	30	9986	VT-1/2

- 1) For valves with G1/8 connection
- Sealing rings included in scope of delivery

Blanking cap VTM

For sealing vacant valve positions

Material:

Wrought aluminium alloy



Ordering data				
Pneumatic connection	Weight [g]	Pa	art No.	Туре
G1/8	5	97	768	VTM-1/8
G1/4	5	97	768	VTM-1/8 ¹⁾
G1/4	7	30	099	VTM-1/4
G1/2	28	99	987	VTM-1/2

1) For valves with G1/8 connection


Solenoid/pneumatic valves, Tiger ClassicAccessories

FESTO

Manifold block PRS

Material: Anodised aluminium





Dimensions	Dimensions and ordering data																		
Туре	B1	B2	В3	B4	D1	D2	D3	H1	H2	Н3	H4	L3	L4	L5	L6	L7	L8	=©1	=© 2
PRS-1/8	28.5	22	12.5	10.8	G1/8	G3/8	6.6	80	56	38	28	23.5	7	27	7	12	5	8	14
PRS-1/4	34.5	27.5	14	14	G1/4	G1/2	6.6	92	62	48	31	29.2	5	31.4	7	14	6	10	17

Number of valve ports	L1	L2	Weight [g]	Part No. Type
Pneumatic connection	on G1/8			
2	81	67	360	11898 PRS-1/8-2
3	108	94	460	11899 PRS-1/8-3
4	135	121	625	11900 PRS-1/8-4
5	162	148	650	11901 PRS-1/8-5
6	189	175	750	11902 PRS-1/8-6
Pneumatic connection	on G1/4			
2	89.8	75.8	590	10185 PRS-1/4-2
3	121.2	107.2	750	10186 PRS-1/4-3
4	152.6	138.6	900	10187 PRS-1/4-4
5	184	170	1070	10188 PRS-1/4-5
6	215.4	201.4	1230	1089 PRS-1/4-6

Hollow bolt

VT

For manifold block PRS

Material:

Anodised aluminium



Ordering data			
Pneumatic connection	Weight	Part No.	Туре
	[g]		
G1/8	17	11539	VT-1/8-PRSK
G1/4	32	9499	VT-1/4-PRS


Solenoid/pneumatic valves, Tiger Classic Accessories

FESTO

Blanking plate PRSB

For sealing vacant valve positions

Material: Aluminium



Ordering data			
Pneumatic connection	Weight	Part No.	Туре
	[g]		
G1/8	55	11687	PRSB-1/8
G1/4	80	11688	PRSB-1/4

Hollow bolt

For separate compressed air supply on valve

Material:

Anodised aluminium



Ordering data			
Pneumatic connection	Weight	Part No.	Туре
	[g]		
G1/8	16	12634	VT-1/8-AJK-P
G1/4	24	12910	VT-1/8-AJS-P ¹⁾
G1/4	45	12635	VT-1/4-AJ-P

¹⁾ For valves with G1/8 connection

Solenoid/pneumatic valves, Tiger Classic Accessories



Ordering data -	Solenoid coils	Technica	al data → Internet: msfg, msfw
	Voltage	Part No.	Туре
F solenoid coils			
90	12 V DC	34410	MSFG-12-OD
	24 V DC and 42 V AC, 50 60 Hz	34411	MSFG-24/42-50/60-OD
	42 V DC	34413	MSFG-42-OD
	24 V AC	34415	MSFW-24-50/60-OD
	48 V AC, 50 60 Hz	34418	MSFW-48-50/60-OD
	110 V AC, 50 60 Hz and 120 V AC, 60 Hz	34420	MSFW-110-50/60-OD
	230 V AC, 50 60 Hz and 240 V AC, 60 Hz	34422	MSFW-230-50/60-0D
	240 V AC, 50 60 Hz	34424	MSFW-240-50/60-OD

Ordering data –	Plug sockets/plug sockets with cable for F so	lenoid coils					
	Voltage	Cable length	LED	Part No.	Туре		
		[m]					
Plug socket without cable Technical data → Internet: mssd							
	-	-	-	34431	MSSD-F		
	-	-	-	539710	MSSD-F-M16		
Diverse elect with a	ut askis with insulation displacement tasks a						
Plug Socket With	out cable with insulation displacement technol			4007//	HCCD F C H47		
	_	_	-	192746	MSSD-F-S-M16		
Plug socket with	cable			T	Technical data 🗲 Internet: kmf		
	24 V DC	2.5		30935	KMF-1-24DC-2,5-LED		
		5		30937	KMF-1-24DC-5-LED		
		10		193458	KMF-1-24DC-10-LED		
	Up to 240 V	2.5	-	30936	KMF-1-230AC-2,5		
		5	-	30938	KMF-1-230AC-5		

Ordering data – Illuminating seal		Technical data → Internet: mf-ld		
	Voltage	Part No.	Туре	
For F solenoid coil	3			
	12 24 V DC	19143	MF-LD-12-24DC	
	230 V DC/V AC	19144	MF-LD-230AC	
		•		

Ordering data – Plate									
	Description		Pneumatic connection	Part No.	Туре				
For wide solenoid coils									
	As spacer when using wider solenoid coils	For 3/2-way valves	G1/8	541667	MPL-TC-3-18				
	om other manufacturers		G1/4	541669	MPL-TC-3-14				
	(thickness: 6.35 mm)	For 5/2-way valves	G1/8	541668	MPL-TC-5-18				
•			G1/4	541670	MPL-TC-5-14				