





Part no.: 50130291
TK 40 x180.1-Set
Reflector

Figure can vary

Contents

- Set consists of
- Technical data
- Dimensioned drawings

Set consists of

	Quantity	Part no.	Designation	Article	Description
	2	50009419	BT 910M	Mounting bracket	Design of mounting device: Angle, L-shape Fastening, at system: Through-hole mounting Mounting bracket, at device: Screw type Type of mounting device: Rigid Material: Metal
	1	50022811	TK 40X180.1	Reflector	Design: Rectangular Reflective surface: 36 mm x 176 mm Triple reflector size: 3 mm Material: Plastic Base material: Plastic Chemical designation of the material: PMMA8N Fastening: Adhesive

Technical data

Mechanical data	
Design	Rectangular
Mounting dimension, width	41 mm
Reflection surface width	36 mm
Mounting dimension, height	181 mm
Reflection surface height	176 mm
Mounting dimension, thickness	8.2 mm
Triple reflector size	3 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Net weight	39 g
Type of fastening	Adhesive

Environmental data	
Ambient temperature, operation	-40 ... 65 °C

Certifications	
Degree of protection	IP 67

Classification	
Customs tariff number	90029000
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467

Dimensioned drawings

All dimensions in millimeters

