




### Description

The 74LVC1G34Q is an automotive-compliant, single buffer gate with a standard push-pull output. The device is designed for operation with a power supply range of 1.65V to 5.5V. The inputs are tolerant to 5.5V allowing this device to be used in a mixed voltage environment. The device is fully specified for partial power down applications using IOFF. The IOFF circuitry disables the output preventing damaging current backflow when the device is powered down.

The gate performs the positive Boolean function:

Y = A

### **Pin Assignments**



### **Features**

- Grade 1 Ambient Temperature Operation: -40°C to +125°C
- Wide Supply Voltage Range from 1.65V to 5.5V
- ± 24mA Output Drive at 3.3V
- CMOS Low Power Consumption
- IOFF Supports Partial-Power-Down Mode Operation
- Inputs Accept up to 5.5V Regardless of Vcc Level
- ESD Protection Tested per AEC-Q100
- Exceeds 2000V Human Body Model (AEC-Q100-002)
- Exceeds 1000V Charged Device Model (AEC-Q100-011)
- Latch-Up Exceeds 100mA (AEC-Q100-004)
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- The 74LVC1G34Q is suitable for automotive applications requiring specific change control; this part is AEC-Q100 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.

https://www.diodes.com/quality/product-definitions/

### **Applications**

- Voltage Level Shifting
- General Purpose Logic
- Power Down Signal Isolation
- Wide Array of Products such as:
  - Automotive Applications within Grade 1 Temperature Range
  - Industrial Computing/Controls/Automation
  - High Reliability Networking/Communications
  - Industrial/Agricultural Equipment

Notes: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.


- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



### **Pin Descriptions**

Pin Name	Description	
NC	No Connection	
А	Data Input	
GND	Ground	
Y	Data Output	
V <sub>CC</sub>	Supply Voltage	

# Logic Diagram



### **Function Table**

Input	Output
Α	Y
Н	Н
L	L

### Absolute Maximum Ratings (Notes 4 & 5)

Symbol	Description	Rating	Unit
ESD HBM	Human Body Model ESD Protection	2	kV
ESD CDM	Charged Device Model ESD Protection	1	kV
Vcc	Supply Voltage Range	-0.5 to 6.5	V
VI	Input Voltage Range	-0.5 to 6.5	V
Vo	Voltage Applied to Output in High Impedance or IOFF State	-0.5 to 6.5	V
Vo	Voltage Applied to Output in High or Low State	-0.5 to V <sub>CC</sub> + 0.5	V
Ік	Input Clamp Current VI < 0	-50	mA
loк	Output Clamp Current	-50	mA
lo	Continuous Output Current	±50	mA
I <sub>CC</sub> , I <sub>GND</sub>	Continuous Current Through V <sub>CC</sub> or GND	±100	mA
TJ	Operating Junction Temperature	-40 to +150	°C
Tstg	Storage Temperature	-65 to +150	°C

Notes: 4. Stresses beyond the absolute maximum can result in immediate failure or reduced reliability. These are stress values and device operation should be within recommend values.

5. Forcing the maximum allowed voltage could cause a condition exceeding the maximum current or conversely forcing the maximum current could cause a condition exceeding the maximum voltage. The ratings of both current and voltage must be maintained within the controlled range.



# Recommended Operating Conditions (Note 6)

Symbol		Parameter	Min	Max	Unit
M		Operating	1.65	5.5	V
Vcc	Operating Voltage	Data retention only	1.5	—	V
		Vcc = 1.65V to 1.95V	$0.65 \times Vcc$	—	
Vін	High-Level Input Voltage	Vcc = 2.3V to 2.7V	1.7	—	V
VIH	nigh-Level input voltage	$V_{CC} = 3V$ to 3.6V	2	—	v
		V <sub>CC</sub> = 4.5V to 5.5V	$0.7 \times V_{CC}$	—	
		V <sub>CC</sub> = 1.65V to 1.95V	—	$0.35 \times V_{CC}$	
.,	Level and here the first	V <sub>CC</sub> = 2.3V to 2.7V	—	0.7	
VIL	Low-Level Input Voltage	V <sub>CC</sub> = 3V to 3.6V	_	0.8	V
		Vcc = 4.5V to 5.5V	_	$0.3 \times V_{CC}$	
VI	Input Voltage		0	5.5	V
Vo	Output Voltage	put Voltage		Vcc	V
		Vcc = 1.65V	—	-4	
		Vcc = 2.3V	_	-8	mA
Let	High-Level Output Current	Vcc = 2.7V	_	-12	
IOH		V/ 2V/	_	-16	
		$V_{CC} = 3V$	—	-24	
		$V_{CC} = 4.5V$	—	-32	
		$V_{CC} = 1.65 V$	_	4	
		$V_{CC} = 2.3 V$	—	8	
Iol	Low-Level Output Current	Vcc = 2.7V	—	12	mA
IOL		Vcc = 3V	—	16	
		VCC = 3V		24	
		$V_{CC} = 4.5V$	_	32	
	land Transition Discons Fall	$V_{CC} = 1.8V \pm 0.15V, 2.5V \pm 0.2V$	—	20	
Δt/ΔV	Input Transition Rise or Fall Rate	$V_{CC} = 3.3V \pm 0.3V$	_	10	ns/V
		$V_{CC} = 5V \pm 0.5V$	—	5	
TA	Operating Free-Air Temperature	_	-40	+125	°C

Note: 6. Unused inputs should be held at  $V_{CC}$  or Ground.



### Electrical Characteristics (All typical values are at V<sub>CC</sub> = 3.3V, T<sub>A</sub> = +25°C)

Cumula al	Parameter	Test Co	u diti o u o	Vcc	-40°	C to +125	°C	l la it
Symbol			Test Conditions		Min	Тур	Max	Unit
			Іон = -100µА	1.65V to 5.5V	Vcc-0.1	_		
			Iон = -4mA	1.65V	0.95	_		
Vон	High Level Output Voltage	VI = VIH	Iон = -8mA	2.3V	1.7	-		V
VOH		VI = VIH	Іон = -12mA	2.7V	1.9	—		v
			Іон = -24mA	3V	2.0	-		
		I <sub>OH</sub> = -32mA	4.5V	3.4	—	—		
			I <sub>OL</sub> = 100μA	1.65V to 5.5V	—	—	0.10	V
		VI = VIL	$I_{OL} = 4mA$	1.65V	—	—	0.70	
			IoL = 8mA	2.3V	—	—	0.45	
Vol	Low Level Output Voltage		$I_{OL} = 12mA$	2.7V	—	_	0.60	
			$I_{OL} = 24mA$	3V	—	—	0.80	
			IoL = 32mA	4.5V	_		0.80	
h	Input Current	VI = 5.5V or GN	ID	0 to 5.5V	—	±0.1	±1	μA
IOFF	Power Down Leakage Current	$V_1$ or $V_0 = 5.5V$		0V	—	—	±2	μA
Icc	Supply Current	V <sub>1</sub> = 5.5V or GND Io = 0		5.5V	_	0.1	4	μΑ
Δlcc	Additional Supply Current	Input at Vcc – 0.6V		3V to 5.5V	—		500	μA
Cı	Input Capacitance	VI = GND to Vc	C	3.3V	_	5.0		pF

### **Package Characteristics**

Symbol	Parameter	Package	Test Conditions	Min	Тур	Мах	Unit
0	Thermal Resistance	SOT25	Nata 7		184	_	0000
θ <sub>JA</sub> Junction-to-Ambient	SOT353	Note 7	_	385	—	°C/W	
0	Thermal Resistance	SOT25	Note 7	_	62	—	°C/W
θις	Junction-to-Case	SOT353	Note 7	_	164	_	°C/W

Note: 7. Device mounted on FR-4 substrate PC board, 2oz copper, with minimum recommended pad layout.

### **Switching Characteristics**

Figure 1 Typical Values at  $T_A = +25^{\circ}C$  and nominal voltages 1.8V, 2.5V, 2.7V, 3.3V, and 5.0V.

Baramator	From	То	Vec	T <sub>A</sub> = -4	0°C to +12	25°C	Unit
Parameter Input Output	Vcc	Min	Тур	Max	Onit		
	tpp A Y		1.8V ± 0.15V	1.0	4.0	11.0	
			2.5V ± 0.2V	0.5	2.6	5.6	
tPD		2.7V	0.5	2.3	5.6	ns	
		3.3V ± 0.3V	0.5	2.0	5.2		
		5.0V ± 0.5V	0.5	1.6	4.1		


### **Operating Characteristics**

$T_A = +2$	5°C
------------	-----


Parameter		Test	Vcc = 1.8V	Vcc = 2.5V	Vcc = 3.3V	Vcc = 5V	Unit
	Falameter	Conditions	Тур	Тур	Тур	Тур	Unit
Cpd	Power Dissipation Capacitance	f = 10MHz	15	16	16	16	pF





### **Measurement Information**



Vcc	In	puts	VM	C∟	RL	
VCC	VI	tr/tr	V IVI	5	NL NL	
1.8V ± 0.15V	Vcc	≤2ns	Vcc/2	30pF	1kΩ	
2.5V ± 0.2V	Vcc	≤2ns	Vcc/2	30pF	500Ω	
2.7V	Vcc	≤2.5ns	1.5V	50pF	500Ω	
3.3V ± 0.3V	3.0V	≤2.5ns	1.5V	50pF	500Ω	
5.0V ± 0.5V	Vcc	≤2.5ns	Vcc/2	50pF	500Ω	







Voltage Waveform Propagation Delay Times Inverting and Non Inverting Outputs


#### Figure 1. Load Circuit and Voltage Waveforms

Notes:

- A. Includes test lead and test apparatus capacitance.
  B. All pulses are supplied at pulse repetition rate ≤ 10MHz.
  C. Inputs are measured separately one transition per measurement.
- D.  $t_{PLH}$  and  $t_{PHL}$  are the same as  $t_{PD}$ .



### Ordering Information (Note 8)




Part Number	Package	Package	Package	7" Tape	and Reel
Fait Nullibei	Code	(Notes 9 & 10)	Size	Quantity	Part Number Suffix
74LVC1G34QSE-7	SE	SOT353	2.15mm × 2.1mm × 1.1mm 0.65mm lead pitch	3000/Tape & Reel	-7
74LVC1G34QW5-7	W5	SOT25	3.0mm × 2.8mm × 1.2mm 0.95mm lead pitch	3000/Tape & Reel	-7


8. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Pad layout as shown in Diodes Incorporated's package outline PDFs, which can be found on our website at http://www.diodes.com/package-outlines.html.
 The taping orientation is located on our website at https://www.diodes.com/assets/Packaging-Support-Docs/ap02007.pdf.

### **Marking Information**

Notes:






Part Number	Package	Identification Code
74LVC1G34QW5-7	SOT25	UKQ
74LVC1G34QSE-7	SOT353	UKQ



### **Package Outline Dimensions**


Please see http://www.diodes.com/package-outlines.html for the latest version.

(1) Package Type: SOT25



SOT25					
Dim	Min	Max	Тур		
Α	0.35	0.50	0.38		
В	1.50	1.70	1.60		
С	2.70	3.00	2.80		
D	-	-	0.95		
н	2.90	3.10	3.00		
J	0.013	0.10	0.05		
К	1.00	1.30	1.10		
L	0.35	0.55	0.40		
м	0.10	0.20	0.15		
Ν	0.70	0.80	0.75		
α	0°	8°	-		
All Dimensions in mm					

#### (2) Package Type: SOT353




SOT353				
Dim	Min	Max	Тур	
A1	0.00	0.10	0.05	
A2	0.90	1.00	0.95	
b	0.10	0.30	0.25	
С	0.10	0.22	0.11	
D	1.80	2.20	2.15	
E	2.00	2.20	2.10	
E1	1.15	1.35	1.30	
е	0.650 BSC			
F	0.40	0.45	0.425	
L	0.25	0.40	0.30	
а	0°	8°		
All Dimensions in mm				



## **Suggested Pad Layout**


Please see http://www.diodes.com/package-outlines.html for the latest version.

(1) Package Type: SOT25



Dimensions	Value
Z	3.20
G	1.60
Х	0.55
Y	0.80
C1	2.40
C2	0.95

#### (2) Package Type: SOT353



Dimensions	Value (in mm)
С	0.650
C1	1.900
G	1.300
Х	0.420
X1	1.720
Y	0.600
Y1	2.500

### **Mechanical Data**

#### SOT25

- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 3
- Weight: 0.0158 grams (Approximate)

#### SOT353

- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.0064 grams (Approximate)



#### **IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2020, Diodes Incorporated

#### www.diodes.com