

## Thread boring bar, internal, left

for holding thread turning inserts for internal machining

**ATORN®**

### Application


For female thread machining for thread turning inserts.

### Version

- precision-engineered steel support, burnished and hardened, with 1.5° pitch angle

### Advantage

- top-quality and wear-resistant steel support with high-strength clamping screw
- precision-engineered insert seat provides extremely precise threads and excellent finish quality



<b>Art. No.</b>	<b>17747 174</b>
<b>ISO name</b>	SIR/L 0032 S16
<b>Suitable for indexable insert size</b>	16
<b>Min. bore diameter</b>	36 mm
<b>Cutting edge diameter</b>	32 mm
<b>Shaft diameter</b>	32 mm
<b>Length</b>	250 mm
<b>Programming size</b>	19.7 mm
<b>Coolant supply</b>	External
<b>Tool design</b>	Left

### EAN-Code

4050293208955