

'Herkules' straightening wedges



Application:

For vertical alignment of complex castings or forgings on machine tools, fine adjustment.

Execution:

- Tempered
- With burnished finish

Advantage:

- The straightening wedge can be adjusted slightly at a load of maximum 1/3 F with just hand force.
- The simple and sturdy design ensures a long service life.
- The fine machined wedge surfaces allow careful and precise adjustment, which means that 0.1 mm can be adjusted with ease, either with a knurled thumb screw or with a hexagon screwdriver.
- The double wedge effect results in a large travel and precise vertical movement without lateral offset.



Art. no.	26170 063
Brand	AMF
Manufacturer Part Number	72777
Size	63
Min./max. support plate height	50-68 mm
Correcting wedge width	40 mm
Width of support plate	63 mm
Support plate length	63 mm
Height adjustment per revolution	0.86 mm
Tension force	40 kN
Weight	1.7 kg
Width across flats	13 mm
Gross Weight	1.570 kg
Product Group	260

EAN

4020772072773