

ITEM	MOLEX P/N	DESCRIPTION	QTY	UOM
A,B	39014041	MiniFit Jr Rec Hsg SR V-0 4Ckt	2	PC
C	39000077	MiniFit Term Crp Fem Chn Bs Tin 16awg	8	PC
D	--	RESIN TPE NAT SANTOPRENE	A/R	KG
E	--	MOLD PART INNER CAP	4	PC
F	--	MASTER BATCH BLACK COLOR	A/R	KG
G	--	RESIN PP RTP 151 A NAT UL94V-0 HF	A/R	KG

FROM	TO	CABLE DESCRIPTION	COLOR
A1	B1	4CX16AWG UNSHD BK UL2464	BLACK
A2	B2		RED
A3	B3		WHITE
A4	B4		GREEN




TABLE		
PART NUMBER	TITLE	L1
2153300405	4CKT OVERMOLDED MINIFIT JR CABLE 500MM	500±10
2153300410	4CKT OVERMOLDED MINIFIT JR CABLE 1M	1000±20
2153300420	4CKT OVERMOLDED MINIFIT JR CABLE 2M	2000±25
2153300430	4CKT OVERMOLDED MINIFIT JR CABLE 3M	3000±30

NOTES:

- MOLDING MATERIAL:
 - INNERCAP: PA66 NYLON RESIN.
 - OVERMOLD: SANTOPRENE TPE RESIN & MASTER BATCH BLACK
 - INNERMOLD: PP NAT UL94V-0
- ELECTRICAL PERFORMANCE:
 - VOLTAGE RATING: 300V AC.
 - THIS PRODUCT MUST PASS 100% CONTINUITY TEST PER MOLEX ES-36586-004.
 - DIELECTRONIC STRENGTH: 500V DC/0.01 SEC.
 - INSULATION RESISTANCE: 20M OHMS
- CONNECTOR VIEWS ARE SHOWN FROM MATING SIDE.
- MECHANICAL PERFORMANCE:
 - CABLE HARNESS SHOULD WITHSTAND AN AXIAL FORCE OF 5KGF FOR ONE MINUTE BETWEEN OVERMOLD AND CONNECTOR WITHOUT PHYSICAL DAMAGE.
 - OVERMOLD SIDE CAN PASS THE BENDING TEST IN 100 CYCLES AT EACH OF 2 PLANES, PER EIA364-41 CONDITION I.

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	CURRENT REV DESC:		molex																										
	<table border="1"> <tr> <th>DIMENSION UNITS</th> <th>SCALE</th> </tr> <tr> <td>mm</td> <td>NTS</td> </tr> </table>	DIMENSION UNITS	SCALE				mm	NTS	<table border="1"> <tr> <th>GENERAL TOLERANCES (UNLESS SPECIFIED)</th> </tr> <tr> <td>ANGULAR TOL ± °</td> </tr> <tr> <td>4 PLACES ±</td> </tr> <tr> <td>3 PLACES ±</td> </tr> <tr> <td>2 PLACES ±</td> </tr> <tr> <td>1 PLACE ±</td> </tr> <tr> <td>0 PLACES ±</td> </tr> </table>		GENERAL TOLERANCES (UNLESS SPECIFIED)	ANGULAR TOL ± °	4 PLACES ±	3 PLACES ±	2 PLACES ±	1 PLACE ±	0 PLACES ±	<table border="1"> <tr> <td>EC NO: 670688</td> <td>2021/07/16</td> </tr> <tr> <td>DRWN: SBS04</td> <td>2021/07/19</td> </tr> <tr> <td>CHK'D: RDESAI01</td> <td>2021/07/19</td> </tr> <tr> <td>APPR: RDESAI01</td> <td>2021/07/19</td> </tr> </table>			EC NO: 670688	2021/07/16	DRWN: SBS04	2021/07/19	CHK'D: RDESAI01	2021/07/19	APPR: RDESAI01	2021/07/19		
DIMENSION UNITS	SCALE																													
mm	NTS																													
GENERAL TOLERANCES (UNLESS SPECIFIED)																														
ANGULAR TOL ± °																														
4 PLACES ±																														
3 PLACES ±																														
2 PLACES ±																														
1 PLACE ±																														
0 PLACES ±																														
EC NO: 670688	2021/07/16																													
DRWN: SBS04	2021/07/19																													
CHK'D: RDESAI01	2021/07/19																													
APPR: RDESAI01	2021/07/19																													
DIVISIONAL SYMBOLS	<table border="1"> <tr> <th>INITIAL REVISION:</th> </tr> <tr> <td>DRWN: SBS04</td> </tr> <tr> <td>APPR: MNARAYAN01</td> </tr> </table>	INITIAL REVISION:	DRWN: SBS04	APPR: MNARAYAN01	<table border="1"> <tr> <th>DOCUMENT NUMBER</th> <th>DOC TYPE</th> <th>DOC PART</th> <th>REVISION</th> </tr> <tr> <td>2153300405</td> <td>PSD</td> <td>000</td> <td>B1</td> </tr> </table>	DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION	2153300405	PSD	000	B1	<table border="1"> <tr> <th>DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</th> <th>THIRD ANGLE PROJECTION</th> <th>DRAWING</th> <th>SERIES</th> <th>MATERIAL NUMBER</th> <th>CUSTOMER</th> <th>SHEET NUMBER</th> </tr> <tr> <td></td> <td></td> <td>A3-SIZE</td> <td>215330</td> <td>SEE TABLE</td> <td>GENERAL MARKET</td> <td>1 OF 1</td> </tr> </table>			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER			A3-SIZE	215330	SEE TABLE	GENERAL MARKET	1 OF 1
INITIAL REVISION:																														
DRWN: SBS04																														
APPR: MNARAYAN01																														
DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION																											
2153300405	PSD	000	B1																											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER																								
		A3-SIZE	215330	SEE TABLE	GENERAL MARKET	1 OF 1																								