

Würth Elektronik eiSos GmbH &amp; Co. KG

EMC &amp; Inductive Solutions

Max-Eyth-Straße 1 · 74638 Waldenburg · Germany

Tel. +49 (0) 79 42 945-0 · Fax +49 (0) 79 42 945-400

eiSos@we-online.de · www.we-online.de



## Product / Process Change Notification (PCN)

- Major change  
 Minor change

**PCN #:** PCN\_IndPMI\_20200316  
**Affected Series:** WE-PMI 1008; 74479887xxxA

**PCN Date:** December 16, 2019  
**Effective Date:** March 16, 2020

### Change Category:

- Equipment / Location  
 General Data  
 Material  
 Process  
 Product Design  
 Shipping / Packaging  
 Supplier  
 Software

**Contact:** Product Management  
**Phone:** +49 (0) 7942 - 945 5001  
**Fax:** +49 (0) 7942 - 945 5179  
**E-Mail:** pcn.eisos@we-online.com

### Data Sheet Change:

- Yes  No

### Attachment:

- Yes  No

### DESCRIPTION AND PURPOSE OF CHANGE:

In order to increase the production capacity of the Product Series WE-PMI, Würth Elektronik will add an additional production line.

### DETAIL OF CHANGE:

The production lines can be identified by the first three digits of the lot number.

1. Lot No. of already established production line:  
 Lot number starting with 187  
 Country of Origin: Taiwan

Lot No. of additional production line:  
 Lot number starting with 241  
 Country of Origin: Taiwan

2. The RDC of 74479887210A will change from 100mOhm to 75mOhm

Würth Elektronik eiSos GmbH &amp; Co. KG

EMC &amp; Inductive Solutions

Max-Eyth-Straße 1 · 74638 Waldenburg · Germany

Tel. +49(0)79 42 945-0 · Fax +49(0)79 42 945-400

eiSos@we-online.de · www.we-online.de



During continues process and product improvement, the RDC has changed for one part.

Part number	Properties		Test conditions	Value old	Value new	Unit	Tol.
74479887210A	DC Resistance	RDC	@ 20°C	100	75	mΩ	±30%
74479887210A	DC Resistance	RDC	@ 20°C	130	97.5	mΩ	max.

Beside of this one change in the RDC, there will be no change in form, fit, function, quality or reliability of the product.

#### RELIABILITY / QUALIFICATION SUMMARY:

Please see the Reliability Overview as below. All Tests were passed

	Test	Qty	Reference	Test conditions
1	High Temperature Exposure (Storage)	30	MIL-STD-202 Method 108	125°C, 1000 hrs.
2	Temperature Cycling	30	JESD22 Method JA-104	1000 cycles (-40°C to +125°C).
3	Biased Humidity	30	MIL-STD-202 Method 103	1000 hours , 85°C, 85%RH. Unpowered.
4	Operational Life	30	MIL-PRF-27	1000 hrs. , 105°C. Unpowered.
5	Resistance to Soldering Heat	30	MIL-STD-202 Method 210	Condition B, No pre-heat of samples. solder temperature : 260 ±5°C Dip time : 10 ±1sec
6	Solderability	30	J-STD-002C	Conditions B1 solder temperature : 255±5 °C Dip time : 5+0/-0.5sec

Reliability test according to AEC-Q200-REV D test requirements