

knurl cutter HSSE PM 15°

For use on knurl cutter tools 19100



Application:

For producing knurls in accordance with DIN 82 RGE 45° (for holders with 2 knurls) and RBR 15° and RBL 15° (for holders with 1 knurl), in the steel, stainless steel, non-ferrous metals and cast iron material groups.

Execution:

- HSSE PM 15°, ground tooth flanks, uncoated

Advantage:

- High precision with ground teeth and good cutting performance, even with difficult materials
- Very good surface quality and long service life with high-quality HSSE-PM cutting material
- coating for increased service life requirements



Art. no.	19163 005
Brand	QUICK
Manufacturer Part Number	42000008
Knurling wheel diameter	8.9 mm
Partition	0.5 mm
Machining direction	Right
Surface	Coated
Gross Weight	0.001 kg
Product Group	192