

## Clamps

With magnetic base



### Version:

- Heat-treated steel
- Painted
- With self-locking trapezoid spindle and end safety device
- With flat support
- Centring hole  $\varnothing$ 12 mm

### Advantage:

- Durable and precise positioning of workpiece thanks to permanent magnet in the base.

<b>Art. no.</b>	<b>26157 130</b>
<b>Min./max. support plate height</b>	60-80 mm
<b>Diameter</b>	50 mm
<b>Head diameter</b>	50 mm
<b>Diameter 2</b>	50 mm
<b>Max. force range</b>	100 kN
<b>Centring diameter</b>	12 mm

### EAN-Code

4020772073367

