

Compressed air dual maintenance unit



Version:

- consisting of filter pressure regulator and compressed air lubricator

Advantage:

- Correct pressure settings and atomised oil ensure a long service life for various pneumatic tools or controls.

Delivery:

Includes plastic container with drain valve for filter and plastic container for lubricator.

Art. no.	75424 040
Connection thread	G 3/4 inch
Air flow	5000 l/min
Container volume, filter	85 cm ³
Container volume, lubricator	125 cm ³
Max. operating pressure	16 bar
Width x height	140 x 273 mm

EAN-Code

4030875099478

