

Dot laser, red, 635 nm, 1 mW

DDI635-1-24(12x45)-C500-NT
Order Number: 70115062

Main Parameters (*)	min	typ	max	Unit
Wavelength		635		nm
Optical Output Power		1		mW
Operating Voltage	21.6	24	26.4	V DC
Operating Current	10	15	25	mA
Operating Temperature	-20		50	°C
Storage Temperature	-40		80	°C

Main Data

Warranty	1 years
----------	---------

Technical Parameters

Lifetime	> 5,000 h
RoHS	yes

Optical Parameters

Beam Shape	Dot
Laser Class	2
Divergence	D - 0.5 mrad
Size of Laserdot	adjustable
Operating Distance	10 m
Optics	glass lens AR coated
Laser technology	diode
Focus	adjustable

Electrical Parameters

Potential of Housing	isolated
Connector	2.1 mm DC socket (+pole inner)

Mechanical Parameters

Size	Ø12x45 mm
Material	aluminium
Cable length	500 mm
Wire type	26AWG, 0,14mm ²
Output Aperture	5 mm
Weight	15 g

(*) Over the complete operating temperature range

Features




- Glas lenses anti reflex coated
- Isolated housing
- Laser Class 2
- Operating Voltage 24 V DC
- Small package


Picture




Cable color

Ground		black	GND
positive		red	21.6 - 26.4, typ 24 V DC

Drawing



Safety Label



Valid Revision

1