

30°, 45°, 60° chamfer cutters for milling inserts TCMT 1102.., TCMT 16T3..


ATORN®

Application

Universal use for chamfering and deburring.

Version

- with straight shank in accordance with DIN 1835 B
- Shaft tolerance h6
- Clamping screw tightening torque (indexable insert) M2.5 = 1.2 Nm, M4 = 5.2 Nm



Art. No.	16107435
Chamfer angle	60 Degree
Max. cutting edge diameter	35 mm
Min. cutting edge diameter	20 mm
Clearance length	39 mm
Length	100 mm
Shaft diameter	25 mm
Number of cutting edges	2 PCS
Suitable indexable insert no.	2
Suitable for indexable inserts	TC.. 16T3..

EAN-Code

4050293111798