

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638275600](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Hand Crimp Tool for Nano-Fit Receptacle Terminals, 20-22 AWG UL1061 wire and 22 AWG UL1007 wire

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207129
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	887191922249
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers
 Application Tooling Documents

ATS-6382756HM-001, TM-638000029-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[207129 Series](#)

Application Tooling Description

FAQ Product #

Nano-Fit Crimp Terminal, Female, 2.54µm Matte Tin (Sn) Plating, 20-22 AWG	1053002100
Nano-Fit Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 20-22 AWG	1053002200
Nano-Fit Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 20-22 AWG	1053002300
Nano-Fit Crimp Terminal, Female, 0.76µm Gold (Au) Plating, Lubricated, 20-22 AWG	1053002400

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION