

PCLN clamp holder, negative, left

For face and longitudinal turning with CN indexable insert

ATORN[®]

Application


For longitudinal and face turning with CN indexable insert, 80°

Version

- Precision-manufactured steel support, burnished, hardened, toggle-joint clamping system, type C, working angle 95°, tip angle 80°, clearance angle 0°

Advantage

- Universal use for face and longitudinal turning with large feed depths and unfavourable conditions
- Negative geometry of the body ensures good stability and force absorption at large cutting depths
- Broad range of use: suitable for both finishing and roughing operations



Art. No.	17837 046
ISO name	PCLN R/L 3225 P16
Shaft height	32 mm
Shank width	25 mm
Length	170 mm
Length of head	34 mm
Programming size	32 mm
Suitable for indexable inserts	CN.. 1606..
Tool design	Left
DIN	4983

EAN-Code

4050293126778