

Revolving high-performance tips

With reinforced bearings



Application:

For use in conjunction with conventional turning, CNC turning, rough machining and smoothing.

Execution:

- 60° moving point.
- For all turning operations (roughing, finishing and fine turning).
- Precision and rough machining of medium-sized components.
- Hardened and precision-ground.

Advantage:

- Long service life.
- Concentricity guaranteed with test report.
- Maintenance-free owing to permanent lubrication.
- Reinforced and hard-wearing precision bearings to absorb radial and axial forces.

Delivery:

1x revolving high-performance tips.



Art. no.	22130 030
Brand	BRUCKNER
Manufacturer Part Number	5003
Morse taper size	MK 3
Programming size	84 mm
Programming size for housing	59 mm
Max. workpiece weight	400 kg
Max. rotation speed	5500 rpm
Concentricity tolerance	0.005 mm
Diameter of housing	45 mm
Tip diameter	20 mm
Gross Weight	1.000 kg
Product Group	2AA