


# Check valve, family E, type B, DN6, PN10, acoustic group I, acc. EN 13959, ST10/DN6

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mittelteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.




Max. operating temperature 65°C,  
 max. 1h at 90°C

### Assembly:


Use pure water or vaseline for assembly

### List of Material:

- O-Ring                   Silicone
- Spring                   Stainless Steel
- Plunger                 POM
- Guidance               POM
- Housing                 POM



Copying of this document, and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of a utility model or design.

<b>NEOPERL Group</b>				
	Date	Name		
Drawn:	Jan. 2012	FE192		<b>Title:</b> <b>check valve</b> <b>DW10/DN6</b>
Appr.:	Jan. 2012	FE183 / FE182		
Scale:				
Format: A4 / US Letter	Page 1 of 1			<b>Part-No.:</b> <b>30.4010.00000</b>
<b>Rev.</b>				
Date:			flow, stop and go®	