



Light-intensive hand-held stroboscope

- Light-intensive
- Stroboscopic
- Memory function




The testo 476 Pocket Strobe™ hand-held stroboscope measures and checks rotation and vibration movements. It facilitates the measurement of very small objects or in hard-to-access places.

The energy optimised switching electronics and light-intensive xenon flash lamp facilitate a high light intensity (approx. 800 lux).

- **High setting accuracy and stability thanks to dynamic setting dial**
- **High light intensity due to energy optimised switching electronics and powerful xenon flash lamp**
- **Powerful rechargeable battery pack for min. 1 hour operation time over the frequency range**
- **Automatic trigger to synchronize flash sequence**



rpm measurement in a turbine, for example



Measure the speed in rapid stroke machines, for example

testo 476

Kit

testo 476, Pocket Strobe™ hand-held stroboscope incl. transport case, recharger with 4 country adapters and trigger signal connector

Part no. 0563 4760

Ordering data for Accessories

	Part no.
Belt bag with clip for hand-held stroboscope	0516 4760
Spare xenon flash lamps (2 off) for hand-held stroboscope	0554 4760
High light intensity	
ISO calibration certificate/rpm	0520 0012
Optical and mechanical rpm measuring instruments; cal. points 500; 1000; 3000 rpm	

Recommended kit:

testo 476, The Affordable Kit



testo 476, Pocket Strobe™ hand-held stroboscope incl. transport case, recharger with 4 country adapters and trigger signal connector

Part no. 0563 4760

Technical data

Meas. range	+30... +12500 rpm	Oper. temp.	0... +40 °C
Accuracy ± 1 digit	±0.01% of mv (+30... +12500 rpm)	Weight	465 g
Resolution	1 rpm (+30... +12500 rpm)	Dimensions	240x65x50 mm
		Warranty	2 years
		Display: 5 digit LCD display	
		Illumination: 800 Lux at distance of approx. 20 cm	
		Flash energy: max. 150 mJ	
		Operating time: 1h at 30 to 12,500 rpm and 23°C (typically)	